


# EA116SB(750W/10Lタンク エアークンプレッサー)



コンデンサー →EB116SB-90(図面なし)

# PARTS LIST

| No. | Parts No.  | Description                        | Q'ty |
|-----|------------|------------------------------------|------|
| 1   | SD1010A-01 | Cylinder Head                      | 1    |
| 2   | SD1010A-02 | Cylinder Head Packing              | 1    |
| 3   | SD1010A-03 | Inlet & Exhaust Valve Seat         | 2    |
| 4   | SD1010A-04 | Inlet & Exhaust Valve Seat Packing | 1    |
| 5   | SD1010A-05 | Inlet & Exhaust Valve Plate        | 2    |
| 6   | SD1010A-06 | Inlet & Exhaust Spring Plate       | 2    |
| 7   | SD1010A-07 | Round Head Bolt                    | 5    |
| 8   | SD1010A-08 | Pin                                | 4    |
| 9   | SD1010A-09 | In Six-Angle Bolt                  | 4    |
| 10  | SD1010A-10 | Spring Washer                      | 4    |
| 11  | SD1010A-11 | Exhaust Elbow                      | 1    |
| 12  | SD1010A-12 | Exhaust Tube Assembly              | 1    |
| 13  | SD1010A-13 | Unloading Elbow                    | 1    |
| 14  | SD1010A-14 | Quick Coupler                      | 1    |
| 15  | SD1010A-15 | Valve Seat Packing                 | 1    |
| 16  | SD1010A-16 | Cylinder                           | 1    |
| 17  | SD1010A-17 | Piston                             | 1    |
| 18  | SD1010A-18 | Compression Ring                   | 2    |
| 19  | SD1010A-19 | Oil Control Ring                   | 1    |
| 20  | SD1010A-20 | Pision Pin                         | 1    |
| 21  | SD1010A-21 | Piston Pin Snap Ring               | 2    |
| 22  | SD1010A-22 | Cylinder Packing                   | 1    |
| 23  | SD1010A-23 | Set Nut                            | 4    |
| 24  | SD1010A-24 | Spring Washer                      | 4    |
| 25  | SD1010A-25 | Double Head Screw                  | 4    |
| 26  | SD1010A-26 | Crankcase                          | 1    |
| 27  | SD1010A-27 | Front Cover Packing                | 1    |
| 28  | SD1010A-28 | Crankshaft                         | 1    |
| 29  | SD1010A-29 | Front Cover                        | 1    |
| 30  | SD1010A-30 | Rod                                | 1    |
| 31  | SD1010A-31 | Oil Gauge                          | 1    |
| 32  | SD1010A-32 | Oil Draining Plug                  | 1    |
| 33  | SD1010A-33 | Motor Cover                        | 1    |
| 34  | SD1010A-34 | In Six-Angle Bolt                  | 4    |
| 35  | SD1010A-35 | Spring Washer                      | 4    |
| 36  | SD1010A-36 | Air Filter                         | 1    |
| 37  | SD1010A-37 | Air Flue Oil Filling Assembly      | 1    |
| 38  | SD1010A-38 | Motor                              | 1    |
| 39  | SD1010A-39 | Radiation Fan                      | 1    |
| 40  | SD1010A-40 | Oil Guage Packing                  | 1    |
| 41  | SD1010A-41 | Air Tank                           | 1    |
| 42  | SD1010A-42 | Pressure Gauge                     | 1    |
| 43  | SD1010A-43 | Regulator Valve                    | 1    |
| 44  | SD1010A-44 | Rubber Handle                      | 1    |
| 45  | SD1010A-45 | Plate Washer                       | 2    |
| 46  | SD1010A-46 | Tank Wheel                         | 2    |
| 47  | SD1010A-47 | Tank Feet Rubber Packing           | 2    |
| 48  | SD1010A-48 | Drain Cock                         | 1    |
| 49  | SD1010A-49 | Check Valve                        | 1    |
| 50  | SD1010A-50 | Pressure Gauge                     | 1    |
| 51  | SD1010A-51 | Brass Five Way Pipe                | 1    |
| 52  | SD1010A-52 | Pressure Switch                    | 1    |
| 53  | SD1010A-53 | Nipple                             | 1    |
| 54  | SD1010A-54 | Unloading Tube                     | 1    |
| 55  | SD1010A-55 | Safety Valve                       | 1    |
| 56  | SD1010A-56 | Cable Wire                         | 1    |
| 57  | SD1010A-57 | Power Wire                         | 1    |
| 58  | SD1010A-58 | Tank Wheel Nut                     | 2    |
| 60  | SD1010A-60 | Circuit Breaker                    | 1    |

SD1010-50/60-P-1103C-VO