品番: EA940AG-621

品名:8 m m x 5m/2芯 ビニールキャブタイヤケーブル



販売価格	7,790円 (税抜)/ 8,569円(税込)					
カタログ価 格	7,790円(税抜)/8,569円(税込)					
在庫数	最新在庫: 2 (2025/11/20 07:22現在)					
商品入数	1	販売単位	本			
カタログページ	1181ページ					





キャブタイヤケ	キャプタイヤケーブルの許容電流					
電線の太さ×心数	電線的容電流(A) VCT/2CT(2PNCT)					
2.0ml×2ii)	22(28)					
// ×3b	19(24)					
// ×40.	17(22)					
3.5ml×2i)	32(41)					
# ×36	28(36)					
// ×40	25(32)					
5.5mb<2i)	41 (53)					
# ×36	36(46)					
# ×40	32(42)					
8.0ml×2i)	51 (65)					
# ×36	44 (56)					
# ×40	39(50)					
14.0ml×2i)	71 (91)					
v v20	627900					



仕様

略号	7/10/1 7/10/1	用途	工事現場などに使用する600V以下の 移動用電気機器の電源や配線などに。
定格容量	51A 600V (8.0m㎡×2心)	長さ	5m
公称断面積	8.0m m ²	仕上外径	16.0mm
曲げ半径	66mm以上	定格温度	移動:-15~60℃ 固定:-30~60℃

ビニル絶縁ビニルシースキャブタイヤケーブル

2心(白:黒)

一般的なVCTに比べ柔軟性に優れ、取り回しが良好です。

移動機器用や配線用として屋外にも対応

PSEマーク取得商品

代替品



品番 EA940AG-622

コメント 長さの違い(5m→10m)

株式会社エスコ

大阪府大阪市西区立売堀3丁目8番14号 06-6532-6226(代表) © 2018 ESCO Co.,Ltd.