品番: EA986VF-50

品名:50mm/200kg 戸車(コ型·重量用)



販売価格	3,120円(税抜)/3,432円(税込)				
カタログ価格	3,120円(税抜)/3,432円(税込)				
在庫数	最新在庫: 8 (2025/11/26 11:41現在)				
商品入数	1	販売単位	個		
カタログページ	1750ページ				



9クタイル検軟と整直検験の比較 MRI (1988) (2017) (807 BC (1989) (1999)







## 仕様

サイズ	A:50mm, B:20mm, B2:39.5× φ9.9mm, C:7.5mm, D:5mm, E:6.2mm, G:64mm, G1:57mm, H:100mm, J:32mm, L:15mm, L1:11mm, P:70mm, t:3.2mm	耐荷重(2個)	200kg		
材質	車:ダクタイル鋳鉄、 枠:鉄板(クロメートメッキ)	重量	0.51kg		
密閉防塵式ベアリング1個					
1個価格					
枠付					

## 株式会社エスコ

大阪府大阪市西区立売堀3丁目8番14号 06-6532-6226(代表) © 2018 ESCO Co.,Ltd.