

品番：EA423RA-11

品名：オーリングセット(26サイズ)(固定用)



販売価格	15,900円(税抜) / 17,490円(税込)		
カタログ価格	15,900円(税抜) / 17,490円(税込)		
在庫数	最新在庫: 4 (2025/08/03 18:26現在)		
商品入数	1	販売単位	St
カタログページ	1352ページ		



EA423RA-11		●規格: JIS B 4801	
S-3	2.5	1.5	(20)
S-4	3.5	1.5	(20)
S-5	4.5	1.5	(20)
S-6	5.5	1.5	(20)
S-7	6.5	1.5	(20)
S-8	7.5	1.5	(20)
S-9	8.5	1.5	(20)
S-10	9.5	1.5	(20)
S-11.2	10.7	1.5	(20)
S-12	11.5	1.5	(20)
S-12.5	12	1.5	(20)
S-14	13.5	1.5	(20)
S-15	14.5	1.5	(20)
S-16	15.5	1.5	(20)
S-18	17.5	1.5	(20)
S-20	19.5	1.5	(20)
S-22	21.5	1.5	(20)
S-22.4	21.9	2	(10)
S-24	23.5	2	(10)
S-25	24.5	2	(10)
S-26	25.5	2	(10)
S-28	27.5	2	(10)
S-29	28.5	2	(10)
S-30	29.5	2	(10)
S-32	31.5	2	(10)
S-35	34.5	2	(10)

仕様

〈セット内容〉JIS番号 / 内径 / 線径 (入数)	S-3 / 2.5 / 1.5(20) S-4 / 3.5 / 1.5(20) S-5 / 4.5 / 1.5(20) S-6 / 5.5 / 1.5(20) S-7 / 6.5 / 1.5(20) S-8 / 7.5 / 1.5(20) S-9 / 8.5 / 1.5(20) S-10 / 9.5 / 1.5(20) S-11.2 / 10.7 / 1.5(20) S-12 / 11.5 / 1.5(20) S-12.5 / 12 / 1.5(20) S-14 / 13.5 / 1.5(20) S-15 / 14.5 / 1.5(20) S-16 / 15.5 / 1.5(20) S-18 / 17.5 / 1.5(20) S-20 / 19.5 / 1.5(20) S-22 / 21.5 / 1.5(20) S-22.4 / 21.9 / 2(10) S-24 / 23.5 / 2(10) S-25 / 24.5 / 2(10) S-26 / 25.5 / 2(10) S-28 / 27.5 / 2(10) S-29 / 28.5 / 2(10) S-30 / 29.5 / 2(10) S-32 / 31.5 / 2(10) S-35 / 34.5 / 2(10)	材質	ニトリルゴム2種
使用温度	-30~100℃	ケースサイズ	280×187×41mm

総重量	379.6g	
円筒面、平面固定用		
耐油性		

株式会社エスコ

大阪府大阪市西区新町4丁目14番12号 06-6532-6226(代表)

© 2018 ESCO Co.,Ltd.