

品番：EA573BE-171

品名：3/16"x114mm [Hexagon]キーレンチ(インチ)



|         |                              |      |   |
|---------|------------------------------|------|---|
| 販売価格    | 90円(税抜)／99円(税込)              |      |   |
| カタログ価格  | 90円(税抜)／99円(税込)              |      |   |
| 在庫数     | 最新在庫: 0 (2025/06/07 23:32現在) |      |   |
| 商品入数    | 1                            | 販売単位 | 本 |
| カタログページ |                              |      |   |



| インチ・ミリ換算表 |        |        |        |
|-----------|--------|--------|--------|
| 1/4"      | 6.35mm | 3/8"   | 9.53mm |
| 1/2"      | 12.7mm | 1/2"   | 12.7mm |
| 1"        | 25.4mm | 1 1/2" | 38.1mm |

| インチ    | ミリ        | インチ    | ミリ        |
|--------|-----------|--------|-----------|
| 1/16"  | 1.5875mm  | 1 1/4" | 31.75mm   |
| 1/8"   | 3.175mm   | 1 3/8" | 34.9375mm |
| 3/16"  | 4.7625mm  | 1 1/2" | 38.1mm    |
| 1/4"   | 6.35mm    | 1 5/8" | 41.2875mm |
| 5/16"  | 7.9375mm  | 1 3/4" | 44.45mm   |
| 3/8"   | 9.525mm   | 1 7/8" | 47.625mm  |
| 7/16"  | 11.1125mm | 2"     | 50.8mm    |
| 1/2"   | 12.7mm    | 2 1/8" | 54.0mm    |
| 9/16"  | 14.2875mm | 2 1/4" | 57.15mm   |
| 5/8"   | 15.875mm  | 2 3/8" | 60.325mm  |
| 11/16" | 17.4625mm | 2 1/2" | 63.5mm    |
| 3/4"   | 19.05mm   | 2 5/8" | 66.675mm  |
| 13/16" | 20.6375mm | 2 3/4" | 69.85mm   |
| 7/8"   | 22.225mm  | 2 7/8" | 73.025mm  |
| 15/16" | 23.8125mm | 3"     | 76.2mm    |
| 1"     | 25.4mm    | 3 1/8" | 79.375mm  |
|        |           | 3 1/4" | 82.55mm   |
|        |           | 3 3/8" | 85.725mm  |
|        |           | 3 1/2" | 88.9mm    |
|        |           | 3 5/8" | 92.075mm  |
|        |           | 3 3/4" | 95.25mm   |
|        |           | 3 7/8" | 98.425mm  |
|        |           | 4"     | 101.6mm   |



仕様

|          |      |        |     |
|----------|------|--------|-----|
| サイズ(インチ) | 3/16 | 軸長(mm) | 114 |
|----------|------|--------|-----|

株式会社エスコ

大阪府大阪市西区新町4丁目14番12号 06-6532-6226(代表)  
© 2018 ESCO Co.,Ltd.