

## VULCAN® 180

## **MULTI-FUNCTION RECHARGEABLE LANTERN**

Lightweight and portable, the Vulcan 180 is designed to burn brighter and run longer to keep you covered on the job site. It features a 180° tilting head that allows you to direct light where you need it. Three white LEDs produce extreme brightness and two ultra-bright blue taillight LEDs provide visibility from behind.







Locking mechanism keeps head in place



Handle clearance accommodates heavy gloves and makes hand-offs easier





High and low modes:

- High for a bright, far-reaching beam: 1,200 lumens; 75,000 candela; 548m beam; runs 5.75 hours
- Low for a less intense beam and longer run time: 350 lumens; 22,000 candela;
  296m beam; runs 16 hours

Taillight LEDs can be programmed on or off

High-impact, super-tough nylon body; head constructed from high grade aluminum encased in super-tough nylon

IPX7 waterproof to 1m submersion; 2m impact resistance tested

Class I, Division 2 Groups A, B, C, D; Class II Division 2 Groups F, G: Class III; Temperature Class T4

Rack meets requirements of NFPA 1901-14.1.10.2 (2016) mounted in any position Meets applicable European Community Directives

7.43" (18.8cm); 2.47 lbs. (1.12kg)

Limited Lifetime Warranty

Visit streamlight.com for full warranty information

#44302 - Vulcan 180 Standard System - 230V AC/12V DC - Yellow

#44303 - Vulcan 180 Standard System - 240V UK AC/12V DC - Yellow

#44304 - Vulcan 180 Standard System - 240V AUS/NZ AC/12V DC - Yellow

###504 Valcair 100 Otaridard Oysterii - 240V //00/142 //0/12V DO - 10/10V

#44301 - Vulcan 180 Standard System - 120V/100V AC/12V DC - Yellow #44307 - Vulcan 180 Std Sys - 120V/100V AC/12V DC - Yellow - Quick Release Strap

#44305 - Vulcan 180 Vehicle Mount System - 12V DC - Yellow