





SPT Series Pencil Grinder

Oil Free Pencil Grinder



SPT SERIES PENCIL GRINDER

Oil Free Pencil Grinder

The SPT Series Pencil Grinder has been designed to include an innovative motor that contains no vanes, rotor or cylinder, minimising maintenance and repair costs. This motor requires no lubrication and eliminates contamination of the work piece.

FEATURES

- Oil free
- Unique motor design
- 100,000 rpm
- Ceramic bearings
- Stainless steel construction
- Roll throttle
- Replacement motor
- Removable collet guard

BENEFITS

- No contamination of workpiece
- Less friction, no wear parts in motor
- Results in a finer finish
- Offers extended service life
- No corrosion to components
- Ideal for continuous use
- Reduces downtime and repair costs
- Accommodates improved access, control and spindle protection



See the tool in action



EA159CP-70

MODEL	SPT100R
Speed (rpm)	100,000
Power (hp)	0.08
Power (watt)	63
Weight (kg)	0.15
Weight (lb)	0.33
Air consumption (m ³ /min)	0.17
Air consumption (cfm)	6
Noise Level	70
Standard Collet (mm)	3
Collet Option (mm)	2.34
Collet Type	CC
Exhaust Type	Rear
Lever Type	Roll

RECOMMENDED CONSUMABLES

Suitable for use with 3mm tungsten carbide burs and 3mm mounted points.



The SPT Series is designed for industries such as aerospace where consistent stock removal and fine finishing are paramount.


REPLACEMENT MOTOR

SPT Series Pencil Grinders offer a replacement motor function that minimises downtime. The replacement motor can be easily installed, with the tool operating as new following motor replacement. Used motors can be returned to ATA for a full service.

Replacement motor part number – RMSPT



RMSPT




Ordering Information


For more information and / or to place an order, please contact ATA Customer Service at:
International Offices: +353 (0) 49 432 6178 or by email sales@atagroup.ie
UK Offices: +44 (0) 1530 261 145 or by email sales@atagroupuk.com
US Offices: +1 330-928-7744 or by email sales@atatools.com
Website: www.atagroup.co



SPT SERIES
Oil Free Pencil Grinder



SPT100R
100,000 RPM





ROLL THROTTLE
Ideal for fine deburring

STAINLESS STEEL CONSTRUCTION
No corrosion and high quality finish

UNIQUE MOTOR DESIGN
Less friction, no wear parts

CERAMIC BEARINGS
Extended service life

REMOVABLE COLLET GUARD
Improved access and control



Stripping Tool Set part Number 990-559-20

Model	R.P.M	m3/min	kg	dB(A)	m/s2
SPT100R	100000 RPM	0.36	0.15	70.0	<2.5

Parts Diagram, 990-290-10 Issue No 041215

- Wear Protective Goggles
- Wear Protective Mask
- Wear Ear Protection
- Replacement Motor
- Oil Free
- Low Noise
- Low Vibration

Ordering Information

For more information and / or to place an order, please contact ATA Customer Service at:
International Offices: +353 (0) 49 432 6178 or by email sales@atagroup.ie
UK Offices: +44 (0) 1530 261 145 or by email sales@atagroupuk.com
US Offices: +1 330-928-7744 or by email sales@atataools.com
Website: www.atagroup.co



International Offices

t: +353 (0) 49 432 6178
f: +353 (0) 49 432 6298

e: sales@atagroup.ie
w: www.atagroup.co

ATA Burs Ltd., IDA Business & Technology Park,
Killygarry, Cavan, Co. Cavan, H12 DK46, Ireland

UK Offices

t: +44 (0) 1530 261 145
f: +44 (0) 1530 262 801

e: sales@atagroupuk.com
w: www.atagroup.co

ATA Garryson Ltd., Spring Road, Ibstock,
Leicestershire, LE67 6LR, United Kingdom

US Offices

t: +1 330-928-7744
f: +1 330-849-2977

e: sales@atatools.com
w: www.atagroup.co

ATA Tools Inc., 238 Marc Drive
Cuyahoga Falls, Ohio 44223