


## EA164HB-41-150 (1<sup>1</sup>/<sub>2</sub>"インパクトソケット)

- 6ポイント
- 差込角 1 1/2"
- Oリングが付属しています。



|                        | サイズ(mm)        | D1(mm)         | D2(mm)         | l(mm)         | L(mm)          | 重量(g)            |
|------------------------|----------------|----------------|----------------|---------------|----------------|------------------|
| EA164HB-41             | 41             | 68             | 86             | 22            | 80             | 2346             |
| <del>EA164HB-42</del>  | <del>42</del>  | <del>70</del>  | <del>86</del>  | <del>22</del> | <del>80</del>  | <del>2330</del>  |
| EA164HB-46             | 46             | 74             | 86             | 26            | 84             | 2360             |
| EA164HB-50             | 50             | 79             | 86             | 27            | 84             | 2400             |
| <del>EA164HB-52</del>  | <del>52</del>  | <del>82</del>  | <del>86</del>  | <del>38</del> | <del>84</del>  | <del>2340</del>  |
| EA164HB-54             | 54             | 84             | 86             | 38            | 84             | 2340             |
| EA164HB-55             | 55             | 85             | 86             | 44            | 90             | 2450             |
| EA164HB-58             | 58             | 88             | 86             | 44            | 90             | 2510             |
| EA164HB-60             | 60             | 91             | 86             | 43            | 90             | 2640             |
| EA164HB-65             | 65             | 97             | 86             | 48            | 95             | 3050             |
| EA164HB-70             | 70             | 103            | 86             | 52            | 100            | 3350             |
| EA164HB-75             | 75             | 108            | 86             | 56            | 105            | 3700             |
| EA164HB-80             | 80             | 115            | 86             | 60            | 110            | 4240             |
| <del>EA164HB-85</del>  | <del>85</del>  | <del>122</del> | <del>86</del>  | <del>60</del> | <del>110</del> | <del>4550</del>  |
| <del>EA164HB-90</del>  | <del>90</del>  | <del>128</del> | <del>86</del>  | <del>60</del> | <del>112</del> | <del>4840</del>  |
| <del>EA164HB-95</del>  | <del>95</del>  | <del>135</del> | <del>127</del> | <del>52</del> | <del>112</del> | <del>5590</del>  |
| <del>EA164HB-100</del> | <del>100</del> | <del>140</del> | <del>127</del> | <del>53</del> | <del>115</del> | <del>6030</del>  |
| <del>EA164HB-105</del> | <del>105</del> | <del>146</del> | <del>127</del> | <del>57</del> | <del>120</del> | <del>6460</del>  |
| <del>EA164HB-110</del> | <del>110</del> | <del>153</del> | <del>127</del> | <del>60</del> | <del>124</del> | <del>7680</del>  |
| <del>EA164HB-115</del> | <del>115</del> | <del>160</del> | <del>127</del> | <del>62</del> | <del>128</del> | <del>8150</del>  |
| <del>EA164HB-120</del> | <del>120</del> | <del>166</del> | <del>127</del> | <del>64</del> | <del>132</del> | <del>8600</del>  |
| <del>EA164HB-125</del> | <del>125</del> | <del>173</del> | <del>127</del> | <del>67</del> | <del>136</del> | <del>9660</del>  |
| <del>EA164HB-130</del> | <del>130</del> | <del>180</del> | <del>127</del> | <del>69</del> | <del>140</del> | <del>10700</del> |
| <del>EA164HB-135</del> | <del>135</del> | <del>186</del> | <del>127</del> | <del>73</del> | <del>145</del> | <del>11920</del> |
| <del>EA164HB-140</del> | <del>140</del> | <del>190</del> | <del>127</del> | <del>76</del> | <del>150</del> | <del>12000</del> |
| <del>EA164HB-150</del> | <del>150</del> | <del>200</del> | <del>127</del> | <del>83</del> | <del>160</del> | <del>13620</del> |

— 線 = 廃番商品