

EA580FS

Wire Stripper No. 7 Magic

WEICON has been developing and producing various types of cable stripper since 1967. These premium quality tools are TÜV-tested, carry the GS seal for verified safety, and were developed taking occupational safety and user-friendliness aspects into account. The WEICON range includes cable strippers, cable dismantling tools, wire strippers and various multifunctional tools for professional users.

Description

The WEICON wire strippers allow flexible and solid conductors to be stripped easily, quickly and evenly. The wire strippers are ergonomically shaped and have an automatic scanner system to determine the cable diameter. This prevents damage to the inner conductor. The product family of wire strippers includes various types which are used in different fields and are tailored to the individual needs of the users. The pincers are used both in trades and in industry and are also suitable for private use.



The WEICON Wire Stripper No. 7-R has a precise adjustment (5-fold) and an optical length scale of 8 – 24mm (5/16 - 1 inch). This allows flexible round cables of 0.5 – 16.0 mm² (24 – 10 AWG) and solid round cables of 0.5 to 10 mm² (18 – 15 AWG) to be stripped. The Wire Stripper No. 7-R is also suitable for two-core, PVC-insulated flat cables of 0.75 – 1.5 mm². An easy-to-access side cutter is integrated into the tool and can be used up to a cable diameter of 3 mm. It also has exchangeable blades.

Technical data

Cable type:	Fine-wired and solid conductors with PVC insulation
Field of use:	Flexible cables 0.5mm ² - 16mm ² , Solid cables 0.5mm ² - 10 mm ²
Inner blade:	Replaceable
Additional benefits:	Side cutter up to max. 3mm Ø
Approval/certificate:	Safety tested by TÜV NORD
Material:	Glass fibre reinforced polyamide
Length:	175 mm
Weight:	216 g
Accessories:	Replacement blade set, item no. 51100006



Note

Working with WEICON Stripping tools is only permitted with potential free wires and conduction.

WEICON GmbH & Co. KG (Headquarter)

Königsberger Str. 255 · DE-48157 Münster
P.O. Box 84 60 · DE-48045 Münster
Germany

Tel. +49 (0) 251 / 93 22-0
Fax +49 (0) 251 / 93 22-244
Fax +49 (0) 251 / 93 22-233 Export
www.weicon.de · info@weicon.de

WEICON Middle East L.L.C.

Jebel Ali Ind Area 3 · P.O. Box 118 216
Dubai · U.A.E

Phone +971 4 880 25 05
Fax +971 4 880 25 09
Mobile +971 50 545 99 83
www.weicon.ae · info@weicon.ae

WEICON Inc.

20 Steckle Place · Unit 20
Kitchener · Ontario · N2E 2C3
Canada

Phone +1 519 896 5252
Fax +1 519 896 5254
Cell +1 519 590 5168
www.weicon.ca · info@weicon.ca

WEICON Kimya Sanayi Tic. Ltd. Şti.

Yenibosna Mahallesi Yalçın Koreş Caddesi
Arifağa Sokak No: 29 Kat: 3
34530 Yenibosna – İstanbul Turkey
www.weicon.biz.tr · info@weicon.biz.tr

WEICON Romania SRL

Str. Podului Nr.1
547176 Budiu Mic (Targu Mures)
www.weicon.com · office@weicon.com