

BB T形四角ボックスレンチ

T-Handle Wrench, Square Drive




4角



Code	mm	D mm	T mm	L ₁ mm	L ₂ mm	d mm	重量 g	箱入数
BB0008	8	16	12	76	80	6	80	-
BB0010	10	19	16	106	90	9	150	-
BB0012	12	23	18	112	110	9	190	-
BB0013	13	23	18	117	110	9	190	-
BB0014	14	26	20	126	130	10	215	-

・ニッケルクロムメッキ



YB Y形ボックスレンチ

Y-Shape Wrench




6角



Code	mm	d mm	D ₁ mm	D ₂ mm	D ₃ mm	L mm	重量 g	箱入数	
YB0810	8×9×10	8	13	14	15.5	80	120	10	EA618GK-1
YB1014	10×12×14	10	15.5	18	21	85	185	10	EA618GK-2
YB1017	10×14×17	11	15.5	21	24.5	95	230	5	EA618GK-3
YB1217	12×14×17	11	18	21	24.5	95	270	5	EA618GK-4
YB1319	13×17×19	13	19	25	28	105	390	5	EA618GK-5
YB1419	14×17×19	13	21	25	28	105	400	5	EA618GK-6
YB1421	14×17×21	13	21	25	30	110	400	5	EA618GK-7
YB1721	17×19×21	13	25	28	30	115	450	-	EA618GK-8
YB1923	19×21×23	13	28	30	33	120	550	-	EA618GK-9

・ニッケルクロムメッキ



LB L形ボックスレンチ

Tire Wrench



6角



Code	mm	D mm	T mm	A mm	L mm	d mm	重量 g	箱入数	
LB0008	8	13	11	30	110	8	55	-	EA618GL-8
LB0010	10	15.5	13	30	180	8	90	10	EA618GL-10
LB0012	12	18	16	35	190	10	140	10	EA618GL-12
LB0013	13	19	17	37	190	10	150	10	EA618GL-13
LB0014	14	21	18	37	200	10	165	10	EA618GL-14
LB0017	17	24.5	20	45	220	11	225	10	EA618GL-17
LB0019	19	28	24	50	230	13	325	5	EA618GL-19
LB0021	21	30	25	50	250	13	370	5	EA618GL-21
LB0022	22	32	27	55	255	13	375	5	EA618GL-22
LB0024	24	34	29	57	265	14	460	5	EA618GL-24
LB0026	26	38	32	63	270	16	610	-	EA618GL-26
LB0027	27	38	33	63	275	16	610	5	EA618GL-27
LB0030	30	44	37	75	280	19	900	5	EA618GL-30
LB0032	32	44	39	75	280	19	850	5	EA618GL-32
LB0036	36	50	44	82	330	22	1,360	-	EA618GL-36
LB0041	41	58	46	90	350	25	1,550	-	EA618GL-41

・ニッケルクロムメッキ (36mm 以下のサイズ)
・パーカー (41mm)

