


EA628PT-11~-187 【P・P製】平織りテープ



- 材質…ポリプロピレン
- 編み方…平織り(経糸(たていと)と緯糸(よこいと)を交互に浮き沈みさせて織るもの。)
- 丈夫で摩擦に強い

線は取扱い中止になった商品です。

品番	色	サイズ			重量約(g)
		厚さ(mm)	幅(mm)	長さ(m)	
EA628PT-11	黒	1.2	20	10	130
EA628PT-12				20	260
EA628PT-12A				25	325
EA628PT-13				50	650
EA628PT-14	濃灰			10	130
EA628PT-15				20	260
EA628PT-15A				25	325
EA628PT-16				50	650
EA628PT-17	灰			10	130
EA628PT-18				20	260
EA628PT-18A				25	325
EA628PT-19				50	650
EA628PT-20	赤	10	130		
EA628PT-21		20	260		
EA628PT-21A		25	325		
EA628PT-22		50	650		
EA628PT-23	青	10	130		
EA628PT-24		20	260		
EA628PT-24A		25	325		
EA628PT-25		50	650		
EA628PT-26	緑	10	130		
EA628PT-27		20	260		
EA628PT-27A		25	325		
EA628PT-28		50	650		
EA628PT-29	白	10	130		
EA628PT-30		20	260		
EA628PT-30A		25	325		
EA628PT-31		50	650		
EA628PT-32	黄	10	130		
EA628PT-33		20	260		
EA628PT-33A		25	325		
EA628PT-34		50	650		
EA628PT-35	OD	10	130		
EA628PT-36		20	260		
EA628PT-36A		25	325		
EA628PT-37		50	650		

品番	色	サイズ			重量約(g)
		厚さ(mm)	幅(mm)	長さ(m)	
EA628PT-41	黒	1.2	25	10	160
EA628PT-42				20	320
EA628PT-42A				25	400
EA628PT-43				50	800
EA628PT-44	濃灰			10	160
EA628PT-45				20	320
EA628PT-45A				25	400
EA628PT-46				50	800
EA628PT-47	灰			10	160
EA628PT-48				20	320
EA628PT-48A				25	400
EA628PT-49				50	800
EA628PT-50	赤	10	160		
EA628PT-51		20	320		
EA628PT-51A		25	400		
EA628PT-52		50	800		
EA628PT-53	青	10	160		
EA628PT-54		20	320		
EA628PT-54A		25	400		
EA628PT-55		50	800		
EA628PT-56	緑	10	160		
EA628PT-57		20	320		
EA628PT-57A		25	400		
EA628PT-58		50	800		
EA628PT-59	白	10	160		
EA628PT-60		20	320		
EA628PT-60A		25	400		
EA628PT-61		50	800		
EA628PT-62	黄	10	160		
EA628PT-63		20	320		
EA628PT-63A		25	400		
EA628PT-64		50	800		
EA628PT-65	OD	10	160		
EA628PT-66		20	320		
EA628PT-66A		25	400		
EA628PT-67		50	800		

品番	色	サイズ			重量約(g)	品番	色	サイズ			重量約(g)
		厚さ(mm)	幅(mm)	長さ(m)				厚さ(mm)	幅(mm)	長さ(m)	
EA628PT-71	黒	1.2	30	10	180	EA628PT-101	黒	1.7	30	10	275
EA628PT-72				20	360	EA628PT-102				20	550
EA628PT-72A				25	450	EA628PT-102A				25	687
EA628PT-73				50	900	EA628PT-103				50	1375
EA628PT-74	濃灰			10	180	EA628PT-104	濃灰			10	275
EA628PT-75				20	360	EA628PT-105				20	550
EA628PT-75A				25	450	EA628PT-105A				25	687
EA628PT-76	灰			50	900	EA628PT-106	灰			50	1375
EA628PT-77				10	180	EA628PT-107				10	275
EA628PT-78				20	360	EA628PT-108				20	550
EA628PT-78A				25	450	EA628PT-108A				25	687
EA628PT-79	赤			50	900	EA628PT-109	赤			50	1375
EA628PT-80		10	180	EA628PT-110	10	275					
EA628PT-81		20	360	EA628PT-111	20	550					
EA628PT-81A		25	450	EA628PT-111A	25	687					
EA628PT-82	青	50	900	EA628PT-112	青	50	1375				
EA628PT-83		10	180	EA628PT-113		10	275				
EA628PT-84		20	360	EA628PT-114		20	550				
EA628PT-84A		25	450	EA628PT-114A		25	687				
EA628PT-85	緑	50	900	EA628PT-115	緑	50	1375				
EA628PT-86		10	180	EA628PT-116		10	275				
EA628PT-87		20	360	EA628PT-117		20	550				
EA628PT-87A		25	450	EA628PT-117A		25	687				
EA628PT-88	白	50	900	EA628PT-118	白	50	1375				
EA628PT-89		10	180	EA628PT-119		10	275				
EA628PT-90		20	360	EA628PT-120		20	550				
EA628PT-90A		25	450	EA628PT-120A		25	687				
EA628PT-91	黄	50	900	EA628PT-121	黄	50	1375				
EA628PT-92		10	180	EA628PT-122		10	275				
EA628PT-93		20	360	EA628PT-123		20	550				
EA628PT-93A		25	450	EA628PT-123A		25	687				
EA628PT-94	OD	50	900	EA628PT-124	OD	50	1375				
EA628PT-95		10	180	EA628PT-125		10	275				
EA628PT-96		20	360	EA628PT-126		20	550				
EA628PT-96A		25	450	EA628PT-126A		25	687				
EA628PT-97		50	900	EA628PT-127		50	1375				

品番	色	サイズ			重量約(g)	品番	色	サイズ			重量約(g)
		厚さ(mm)	幅(mm)	長さ(m)				厚さ(mm)	幅(mm)	長さ(m)	
EA628PT-131	黒	1.7	38	10	450	EA628PT-161	黒	1.7	48	10	450
EA628PT-132				20	900	EA628PT-162				20	900
EA628PT-132A				25	1125	EA628PT-162A				25	1125
EA628PT-133				50	2250	EA628PT-163				50	2250
EA628PT-134	濃灰			10	450	EA628PT-164	濃灰			10	450
EA628PT-135				20	900	EA628PT-165				20	900
EA628PT-135A				25	1125	EA628PT-165A				25	1125
EA628PT-136				50	2250	EA628PT-166				50	2250
EA628PT-137	灰			10	450	EA628PT-167	灰			10	450
EA628PT-138				20	900	EA628PT-168				20	900
EA628PT-138A				25	1125	EA628PT-168A				25	1125
EA628PT-139				50	2250	EA628PT-169				50	2250
EA628PT-140	赤			10	450	EA628PT-170	赤			10	450
EA628PT-141				20	900	EA628PT-171				20	900
EA628PT-141A				25	1125	EA628PT-171A				25	1125
EA628PT-142				50	2250	EA628PT-172				50	2250
EA628PT-143	青	10	450	EA628PT-173	青	10	450				
EA628PT-144		20	900	EA628PT-174		20	900				
EA628PT-144A		25	1125	EA628PT-174A		25	1125				
EA628PT-145		50	2250	EA628PT-175		50	2250				
EA628PT-146	緑	10	450	EA628PT-176	緑	10	450				
EA628PT-147		20	900	EA628PT-177		20	900				
EA628PT-147A		25	1125	EA628PT-177A		25	1125				
EA628PT-148		50	2250	EA628PT-178		50	2250				
EA628PT-149	白	10	450	EA628PT-179	白	10	450				
EA628PT-150		20	900	EA628PT-180		20	900				
EA628PT-150A		25	1125	EA628PT-180A		25	1125				
EA628PT-151		50	2250	EA628PT-181		50	2250				
EA628PT-152	黄	10	450	EA628PT-182	黄	10	450				
EA628PT-153		20	900	EA628PT-183		20	900				
EA628PT-153A		25	1125	EA628PT-183A		25	1125				
EA628PT-154		50	2250	EA628PT-184		50	2250				
EA628PT-155	OD	10	450	EA628PT-185	OD	10	450				
EA628PT-156		20	900	EA628PT-186		20	900				
EA628PT-156A		25	1125	EA628PT-186A		25	1125				
EA628PT-157		50	2250	EA628PT-187		50	2250				