

CAUTION

To prevent the 3310 flashlight coming on accidentally when the flashlight is stored, remove the batteries. If the 3310 flashlight is turned on while it is in a container, the flashlight can overheat and damage the flashlight or the material of the surrounding area.

Battery Safety Bulletin Alkaline Batteries

- For those lights with hazardous location safety approvals for explosive environments please be advised that the safety approval is only valid for the specified battery type manufacturer and, where applicable, brand names that are displayed on the flashlight and/or instructions sheets that are supplied with the light. The use of other battery technologies may reduce the performance of the flashlight and will invalidate the safety approval.
- Always read the battery manufacturers recommendations for the appropriate use of the battery technology/brand prior to using the flashlight.
- When replacing the batteries:
 - Replace all the batteries at the same time.
 - Do not mix battery brands and old and new batteries.
 - Always insert batteries correctly with regard to polarity (+ and -) marked on the battery and equipment.
- Do not change batteries in a hazardous location.
- Remove batteries from equipment if it is not to be used for an extended period of time.

PELICAN LIMITED LIFETIME GUARANTEE OF EXCELLENCE

Pelican Products, Inc. guarantees its lights for a lifetime against breakage or defects in workmanship. This guarantee does not cover the lamp or batteries. Pelican will either repair or replace any defective product, at our sole option. TO THE EXTENT PERMITTED BY LAW, THE REMEDIES HEREBY PROVIDED SHALL BE THE EXCLUSIVE AND SOLE REMEDY OF THE PURCHASER.

TO THE EXTENT PERMITTED BY LAW: (A) THIS WARRANTY IS IN LIEU OF ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE; AND (B) ALL OTHER IMPLIED WARRANTIES AND ANY LIABILITY NOT BASED UPON CONTRACT ARE HERBY DISCLAIMED AND EXCLUDED.

TO THE EXTENT PERMITTED BY LAW, IN NO EVENT SHALL PELICAN BE LIABLE FOR ANY INDIRECT, PUNITIVE, INCIDENTAL OR CONSEQUENTIAL DAMAGES, OR SPECIAL DAMAGES, REGARDLESS OF WHETHER A CLAIM FOR SUCH DAMAGES IS BASED ON WARRANTY, CONTRACT, NEGLIGENCE OR OTHERWISE. To the extent permitted by law, in no event shall Pelican's liability to the purchaser for damages hereunder exceed the purchase price of the product in respect of which damages are claimed.

To make a warranty claim, the purchaser must contact Pelican Products, Inc. at 23215 Early Avenue, Torrance, CA 90505 or cswwarranty@pelican.com, or by calling 1-800-473-5422, extension 5. Any warranty claims shall be made by the purchaser as soon as practicable. The purchaser must obtain a return authorization number from Pelican Customer Service prior to returning any product, and is responsible for paying for all warranty freight costs. If Pelican determines that any returned product is not defective, within the terms of this warranty, the purchaser shall pay Pelican all costs of handling, return freight and repairs at Pelican's prevailing rates.

All warranty claims of any nature are barred if the flashlight has been altered, damaged or in any way physically changed, or subjected to abuse, misuse, negligence or accident. Some states and countries do not allow limitations on how long an implied warranty lasts or the exclusion or limitation of incidental or consequential damages, so the above limitation or exclusion may not apply to you. This warranty gives you specific legal rights, and you may have other rights which vary from state to state and country to country.

In Australia: The benefits provided to you under this warranty are in addition to your rights and remedies as a consumer under the Competition and Consumer Act 2010 (Cth). Nothing in this warranty limits the rights or obligations of a party under provisions of the Competition and Consumer Act 2010 (Cth) in relation to the supply to consumers of goods which cannot be limited, modified or excluded. If applicable, our goods come with guarantees that cannot be excluded under the Australian Consumer Law. You are entitled to a replacement or refund for a major failure and compensation for any other reasonably foreseeable loss or damage. You are also entitled to have the goods repaired or replaced if the goods fail to be of acceptable quality and the failure does not amount to a major failure. If you are not a consumer under the Competition and Consumer Act 2010 (Cth), then your rights may be limited.

To make a warranty claim, the purchaser must contact Pelican Products Australia, Suite 2.33, West Wing, Platinum Bldg., Erina NSW 2250, Tel: +612 4367 7022. Any warranty claims shall be made by the purchaser as soon as practicable. The purchaser must obtain a return authorization number from Pelican Customer Service prior to returning any product, and is responsible for paying for all warranty freight costs. If Pelican determines that any returned product is not defective, within the terms of this warranty, the purchaser shall pay Pelican all costs of handling, return freight and repairs at Pelican's prevailing rates. In the event that Pelican determines that any returned product is defective, within the terms of this warranty, Pelican shall pay the purchaser all reasonable costs of the purchaser in making claim under this warranty.

Lifetime Guarantee does not cover Roto Molded cases, AALG products or fabric portion of backpacks. Refer to www.pelican.com/warranty for full details.

LA LÉGENDAIRE GARANTIE D'EXCELLENCE À VIE DE PELICAN.

Pelican Products, Inc., garantit ses éclairages pour toute la durée de leur vie utile contre la casse et les défauts de fabrication. Cette garantie ne couvre pas les ampoules ni les batteries (alcalines ou rechargeables).

Pelican réparera ou remplacera tout produit défectueux, à sa seule discrétion. LES RECOURS MENTIONNÉS ICI CONSTITUENT LES SEULS RECOURS DE L'ACHETEUR.

DANS LA MESURE PERMISE PAR LA LOI, EN AUCUN CAS PELICAN NE SERA TENU RESPONSABLE D'AUCUN DOMMAGE IMMATÉRIEL, PUNITIF, ACCESSOIRE OU INDIRECT NI D'AUCUN DOMMAGE PARTICULIER, QU'UNE RÉCLAMATION POUR DE TELS DOMMAGES SE BASE OU NON SUR UNE GARANTIE, UN CONTRAT, UNE NEGLIGENCE OU AUTRE. En aucun cas la responsabilité de Pelican envers l'acheteur en cas de dommages ne sera supérieure au prix d'achat du produit pour lequel des dommages et intérêts sont réclamés.

Pour déposer une demande de prise en charge sous garantie, l'acheteur doit contacter Pelican Products, Inc., à l'adresse suivante : 23215 Early Avenue, Torrance, CA 90505, États-Unis, ou envoyer un courrier électronique à l'adresse suivante : sales@pelican.com. Toute demande de prise en charge sous garantie sera déposée par l'acheteur dès que possible. Avant de retourner tout produit, l'acheteur doit obtenir un numéro d'autorisation de retour du Service Client de Pelican. Au cas où Pelican considérerait qu'un produit retourné n'est pas défectueux, selon les conditions de la présente garantie, l'acheteur rembourse Pelican de tous les frais de manipulation, transport et réparation aux taux en vigueur de Pelican.

Toute demande de prise en charge sous garantie, de quelque nature que ce soit, sera refusée si la torche a été modifiée, endommagée ou physiquement changée d'une façon ou d'une autre ou encore sujette à un traitement abusif, une mauvaise utilisation, une négligence ou un accident.

Certains États n'autorisent pas l'exclusion ou la limitation des dommages accessoires ou indirects, de telle sorte que la limitation ou l'exclusion mentionnée ci-dessus peut ne pas s'appliquer dans votre cas.

La présente garantie vous donne des droits légaux spécifiques et vous pouvez bénéficier d'autres droits, variables d'un État à l'autre.

La garantie à vie ne couvre pas les produits rotomoulés ou AALG. Pour obtenir des informations complètes, visitez le site www.pelican.com/warranty.



23215 Early Ave. • Torrance, CA 90505 USA

Tel (310) 326-4700 • FAX (310) 326-3311

www.pelican.com

PELICAN CANADA ULC

10221-184 St. • Edmonton, Alberta T5S 2J4

Tel (780) 481-6076 • FAX (780) 481-9586

003313-3110-000 5-10791 Rev A

© 2014 Pelican Products MY/14

All trademarks are registered and/or unregistered trademarks of Pelican Products, Inc., its subsidiaries and/or affiliates.

Cat. #3310

PELICAN™

3310

INTRODUCTION

This compact flashlight produces an ultra bright light beam by using an LED powered by (3) three AA 1.5V alkaline batteries. The 3310 flashlight is designed for easy use with one hand operation. The 3310 flashlight body is made of a photoluminescent high impact polymer alloy for the most durable construction. The 3310 flashlight is water resistant.

REMOVE MYLAR INSULATOR BEFORE USE

- Ensure that the tail cap lock is set in the 'Unlock' position.
- Twist the tail cap counter-clockwise until it stops and pull tail cap away from the body.
- Remove and discard the Mylar insulator.
- Replace tail cap, turn clockwise until it aligns with the body.

For added security, turn the tail cap lock to the 'Lock' position with the lanyard attachment.

TO OPERATE

-High > Low > Flashing > Off

- Fully depress switch to activate light. The light will default to the High Mode.
- Once in High Mode, partially depress switch once to obtain the Low Mode, twice to obtain Flashing Mode.
- While activated in any mode, fully depress switch to turn Off.

BATTERY REPLACEMENT

- Repeat previous battery door removal.
- Replace ALL batteries with fresh AA batteries as per polarity markings.
- Replace tail cap, turn clockwise until it aligns with the body.
- For added security, turn the tail cap lock to the 'Lock' position with the lanyard attachment.

GENERAL CARE AND MAINTENANCE

- Clean o-ring with a soft clean cloth to insure that sealing area is free of dirt that could destroy the o-ring seal.
- Apply a light coat of clear silicone grease on the o-ring occasionally.