




**[VE管用]露出ボックス**

赤線の引かれている品番は廃番になりました。

EA940CS-121～-167



品番	カラー	種類	適合管	サイズ(mm)			
				ΦD1	ΦD2	ℓ	H
EA940CS-121	ベージュ	1方出	VE16	26	91	28	38
EA940CS-122			VE22	30	91	33	41
EA940CS-123			VE28	40	105	40	47
EA940CS-124			VE36	50	115	44	57
EA940CS-126	グレー	1方出	VE16	26	91	28	38
EA940CS-127			VE22	30	91	33	41
EA940CS-128			VE28	40	105	40	47
EA940CS-129			VE36	50	115	44	57
EA940CS-131	ベージュ	2方出(S)	VE16	26	91	28	38
EA940CS-132			VE22	30	91	33	41
EA940CS-133			VE28	40	105	40	47
EA940CS-134			VE36	50	115	44	57
EA940CS-136	グレー	2方出(S)	VE16	26	91	28	38
EA940CS-137			VE22	30	91	33	41
EA940CS-138			VE28	40	105	40	47
EA940CS-139			VE36	50	115	44	57

品番	カラー	種類	適合管	サイズ(mm)			
				ΦD1	ΦD2	ℓ	H
EA940CS-141	ベージュ	2方出(L)	VE16	26	91	28	38
EA940CS-142			VE22	30	91	33	41
EA940CS-143			VE28	40	105	40	47
EA940CS-144			VE36	50	115	44	57
EA940CS-146	グレー	2方出(L)	VE16	26	91	28	38
EA940CS-147			VE22	30	91	33	41
EA940CS-148			VE28	40	105	40	47
EA940CS-149			VE36	50	115	44	57
EA940CS-151	ベージュ	3方出	VE16	26	91	28	38
EA940CS-152			VE22	30	91	33	41
EA940CS-153			VE28	40	105	40	47
EA940CS-154			VE36	50	115	44	57
EA940CS-156	グレー	3方出	VE16	26	91	28	38
EA940CS-157			VE22	30	91	33	41
EA940CS-158			VE28	40	105	40	47
EA940CS-159			VE36	50	115	44	57
EA940CS-161	ベージュ	4方出	VE16	26	91	28	38
EA940CS-162			VE22	30	91	33	41
EA940CS-163			VE28	40	105	40	47
EA940CS-164			VE36	50	115	44	57
EA940CS-166	グレー	4方出	VE16	26	91	28	38
EA940CS-167			VE22	30	91	33	41
EA940CS-168			VE28	40	105	40	47
EA940CS-169			VE36	50	115	44	57

・JIS C8435

・カプセ蓋

☆照明器具等の重量物を取り付けしないで下さい。