


ナベ頭小ねじ[ユニクロ]
EA949NE-204~850



●材質…鉄(ユニクロメッキ)

品番	呼び	十字穴 番号	サイズ(mm)					入数	重量(g)
			ℓ	ピッチ	dk	k	m		(1個)
EA949NE-204	M2	1	4	0.40	3.50	1.30	2.20	80	0.14
EA949NE-205			5						0.14
EA949NE-208			8						0.22
EA949NE-210			10						0.25
EA949NE-212			12						0.29
EA949NE-215			15						0.35
EA949NE-220			20						0.43
EA949NE-225			25						0.52
EA949NE-230			30						0.61
EA949NE-305			M3						2
EA949NE-308	8	0.59							
EA949NE-310	10	0.67							
EA949NE-312	12	0.76							
EA949NE-315	15	0.89							
EA949NE-320	20	1.10							
EA949NE-325	25	1.31							
EA949NE-330	30	1.52							
EA949NE-335	35	1.74							
EA949NE-340	40	1.95							
EA949NE-345	45	2.12							
EA949NE-350	50	2.30							
EA949NE-405	M4	2	5	7.00	7.00	2.60	4.20	44	0.85
EA949NE-408			8						1.14
EA949NE-410			10						1.30
EA949NE-412			12						1.45
EA949NE-415			15						1.67
EA949NE-420			20						2.05
EA949NE-425			25						2.42
EA949NE-430			30						2.80
EA949NE-435			35						3.17
EA949NE-440			40						3.55
EA949NE-445	45	3.92							
EA949NE-450	50	4.30							

品番	呼び	十字穴 番号	サイズ(mm)					入数	重量(g) (1個)
			ℓ	ピッチ	dk	k	m		
EA949NE-508	M5	2	8	0.80	9.00	3.30	4.90	28	2.11
EA949NE-510			10					27	2.35
EA949NE-512			12					26	2.59
EA949NE-515			15					22	2.96
EA949NE-520			20					19	3.56
EA949NE-525			25					17	4.16
EA949NE-530			30					14	4.76
EA949NE-535			35					11	5.36
EA949NE-540			40					10	5.97
EA949NE-545			45					9	6.57
EA949NE-550			50					8	7.17
EA949NE-608			M6					3	8
EA949NE-610	10	18		3.93					
EA949NE-612	12	16		4.27					
EA949NE-615	15	15		4.79					
EA949NE-620	20	13		5.64					
EA949NE-625	25	11		6.50					
EA949NE-630	30	9		7.36					
EA949NE-635	35	8		8.22					
EA949NE-640	40	7		9.08					
EA949NE-645	45	6		9.94					
EA949NE-650	50	6		10.80					
EA949NE-810	M8	3		10	1.25	14.00	5.20		7.80
EA949NE-812			12	6				9.31	
EA949NE-815			15	6				10.25	
EA949NE-820			20	5				11.81	
EA949NE-825			25	4				13.37	
EA949NE-830			30	4				14.93	
EA949NE-835			35	3				16.49	
EA949NE-840			40	3				18.05	
EA949NE-845			45	3				19.61	
EA949NE-850			50	2				21.17	