


割ピン[三価クロメート]
EA949PF-161~550



●材質…鉄(三価クロメートメッキ)

三価クロメートとは

三価クロメートとは、通常、亜鉛メッキ後の後処理として耐食性付与のため、三価クロムのクロメート(クロム酸塩)の薄い皮膜を付けることをいいます。外観色調はユニクロに近いものとなります。クロメート処理をするものは、亜鉛メッキと亜鉛合金メッキ、アルミクロメートの3種がほとんどです。

品番	呼び	サイズ(mm)					入数 (個)	重量(g) (1個)
		L	d	D	A	H		
EA949PF-161	1.6	10	1.40	2.80	3.20	2.50	39	0.18
EA949PF-162		15					38	0.24
EA949PF-163		20					31	0.30
EA949PF-164		28					22	0.43
EA949PF-210	2	10	1.80	3.60	4.00	2.50	30	0.30
EA949PF-215		15						0.40
EA949PF-220		20					25	0.50
EA949PF-225		25					22	0.60
EA949PF-230		30					18	0.70
EA949PF-235		35					15	0.80
EA949PF-240		40					13	0.90
EA949PF-245		45					11	1.00
EA949PF-250		50					10	1.01
EA949PF-251		2.5					10	2.30
EA949PF-252	15			0.69				
EA949PF-253	20		22	0.85				
EA949PF-254	25		18	1.01				
EA949PF-255	30		15	1.18				
EA949PF-256	35		13	1.34				
EA949PF-257	40		11	1.50				
EA949PF-258	45		10	1.67				

廃番

品番	呼び	サイズ(mm)					入数 (個)	重量(g) (1個)
		L	d	D	A	H		
EA949PF-315	3	15	2.80	5.60	6.00	3.20	18	1.14
EA949PF-320		20					17	1.40
EA949PF-325		25					14	1.66
EA949PF-330		30					12	1.92
EA949PF-335		35					11	2.18
EA949PF-340		40					9	2.44
EA949PF-345		45					8	2.70
EA949PF-350		50					7	2.96
EA949PF-351	3.5	25	3.30	6.60	7.00	3.20	10	2.87
EA949PF-352		35					7	3.71
EA949PF-353		40					6	4.14
EA949PF-354		45					6	4.56
EA949PF-355		50					5	4.98
EA949PF-420	4	20	3.70	7.40	8.00	4.00	11	2.45
EA949PF-425		25					10	2.87
EA949PF-430		30					8	3.29
EA949PF-435		35					7	3.71
EA949PF-440		40					6	4.14
EA949PF-445		45					5	4.56
EA949PF-450		50					5	4.98
EA949PF-451		4.5					20	4.10
EA949PF-452	25		7	4.70				
EA949PF-453	30		6	5.35				
EA949PF-454	35		5	6.00				
EA949PF-455	40		4	6.65				
EA949PF-456	45		4	7.31				
EA949PF-457	50		4	8.09				
EA949PF-520	5		20	4.60	9.20	10.00	4.00	
EA949PF-525		25	6					4.70
EA949PF-530		30	5					5.35
EA949PF-535		35	4					6.00
EA949PF-540		40	4					6.65
EA949PF-545		45	4					7.31
EA949PF-550		50	3					8.09