



六角頭全ねじボルト EA949LA-306~1290



- 材質…鉄
- ユニクロメッキ

品番	呼び	サイズ(mm)					入数					
		ℓ	ピッチ	k	s	e						
EA949LA-306	M3	6	0.50	2.00	5.50	6.40	17					
EA949LA-308		8					18					
EA949LA-310		10					16					
EA949LA-312		12					15					
EA949LA-315		15					15					
EA949LA-316		16					14					
EA949LA-318		18					15					
EA949LA-320		20					12					
EA949LA-322		22					9					
EA949LA-325		25										
EA949LA-330		30										
EA949LA-335		35										
EA949LA-406		M4					6	0.70	2.80	7.00	8.10	14
EA949LA-408							8					20
EA949LA-410	10		21									
EA949LA-412	12		19									
EA949LA-414	14		20									
EA949LA-415	15		16									
EA949LA-416	16		14									
EA949LA-418	18		11									
EA949LA-420	20		10									
EA949LA-422	22		9									
EA949LA-425	25											
EA949LA-430	30											
EA949LA-435	35											
EA949LA-440	40											
EA949LA-445	45											
EA949LA-450	50											

品番	呼び	サイズ(mm)					入数
		ℓ	ピッチ	k	s	e	
EA949LA-506	M5	6	0.80	3.50	8.00	9.20	10
EA949LA-508		8					17
EA949LA-510		10					
EA949LA-512		12					
EA949LA-514		14					
EA949LA-515		15					
EA949LA-516		16					16
EA949LA-518		18					17
EA949LA-520		20					
EA949LA-522		22					14
EA949LA-525		25					
EA949LA-530		30					13
EA949LA-535		35					12
EA949LA-540		40					11
EA949LA-545		45					10
EA949LA-550		50					9
EA949LA-610	M6	10	1.00	4.00	10.00	11.50	20
EA949LA-612		12					21
EA949LA-614		14					
EA949LA-615		15					20
EA949LA-616		16					
EA949LA-618		18					
EA949LA-620		20					
EA949LA-622		22					
EA949LA-625		25					17
EA949LA-628		28					
EA949LA-632		32					16
EA949LA-640		40					14
EA949LA-645		45					13
EA949LA-650		50					12
EA949LA-810	M8	10	1.25	5.50	13.00	19.60	9
EA949LA-812		12					11
EA949LA-814		14					
EA949LA-815		15					11
EA949LA-816		16					
EA949LA-818		18					
EA949LA-820		20					
EA949LA-822		22					10
EA949LA-825		25					
EA949LA-828		28					9
EA949LA-830		30					7
EA949LA-832		32					
EA949LA-835		35					8
EA949LA-840		40					7
EA949LA-845		45					
EA949LA-850		50					6

品番	呼び	サイズ(mm)					入数
		ℓ	ピッチ	k	s	e	
EA949LA-1012	M10	12	1.50	7.00	17.00	19.60	10
EA949LA-1014		14					12
EA949LA-1015		15					13
EA949LA-1016		16					
EA949LA-1018		18					
EA949LA-1020		20					11
EA949LA-1022		22					
EA949LA-1025		25					10
EA949LA-1028		28					
EA949LA-1030		30					9
EA949LA-1032		32					
EA949LA-1035		35					8
EA949LA-1040		40					
EA949LA-1045		45					7
EA949LA-1050		50					
EA949LA-1055		55					6
EA949LA-1060		60					
EA949LA-1065		65					5
EA949LA-1070		70					
EA949LA-1075		75					4
EA949LA-1080	80						
EA949LA-1085	85						
EA949LA-1090	90						
EA949LA-1215	M12	15	1.75	8.00	19.00	21.90	6
EA949LA-1216		16					7
EA949LA-1218		18					
EA949LA-1220		20					6
EA949LA-1222		22					
EA949LA-1225		25					7
EA949LA-1230		30					
EA949LA-1232		32					5
EA949LA-1235		35					
EA949LA-1245		45					6
EA949LA-1250		50					
EA949LA-1255		55					5
EA949LA-1260		60					
EA949LA-1265		65					4
EA949LA-1270		70					
EA949LA-1275		75					3
EA949LA-1280		80					
EA949LA-1285		85					2
EA949LA-1290	90						