

EA952SA-31～-401

(引きスプリング[1m])

品番	外径	線径	許容荷重
	mm		kgf
EA952SA-31	3	0.4	0.4
EA952SA-41	4	0.3	0.1
EA952SA-42	4	0.5	0.6
EA952SA-51	5	0.5	0.6
EA952SA-52	5	1.2	9.0
EA952SA-61	6	0.5	0.5
EA952SA-62	6	0.8	1.7
EA952SA-71	7	0.5	0.3
EA952SA-72	7	1.2	5.1
EA952SA-81	8	0.5	0.3
EA952SA-82	8	1.2	4.6
EA952SA-91	9	0.6	0.4
EA952SA-101	10	0.6	0.4
EA952SA-102	10	1.2	3.7
EA952SA-111	11	0.6	3.4
EA952SA-112	11	1	1.8
EA952SA-121	12	0.6	0.3
EA952SA-122	12	1	1.7
EA952SA-123	12	1.4	4.6
EA952SA-124	12	1.8	10.3
EA952SA-131	13	1.8	8.0
EA952SA-141	14	1	1.2
EA952SA-142	14	1.6	5.2
EA952SA-143	14	2	10.9
EA952SA-151	15	1.2	2.0
EA952SA-152	15	1.8	6.8
EA952SA-161	16	1.2	1.8
EA952SA-162	16	2	9.6

品番	外径	線径	許容荷重
	mm		kgf
EA952SA-163	16	2.6	20.3
EA952SA-171	17	1.2	1.7
EA952SA-172	17	1.8	5.7
EA952SA-173	17	2.3	12.2
EA952SA-181	18	1.2	1.5
EA952SA-182	18	2	7.4
EA952SA-183	18	2.6	17.4
EA952SA-184	18	3	29.3
EA952SA-191	19	1.6	3.3
EA952SA-192	19	2.3	11.5
EA952SA-193	19	3	27.8
EA952SA-201	20	1.6	3.1
EA952SA-202	20	2	6.9
EA952SA-203	20	2.6	16.0
EA952SA-204	20	3	26.0
EA952SA-205	20	3.5	40.8
EA952SA-206	20	4	69.0
EA952SA-211	21	1.8	4.9
EA952SA-212	21	4	65.4
EA952SA-221	22	1.8	4.3
EA952SA-222	22	2	6.0
EA952SA-223	22	2.6	13.6
EA952SA-224	22	3	21.2
EA952SA-225	22	3.5	34.5
EA952SA-226	22	4	56.5
EA952SA-231	23	2	5.7
EA952SA-232	23	3.5	33.7
EA952SA-241	24	2	5.5

品番	外径	線径	許容荷重
	mm		kgf
EA952SA-242	24	2.6	12.2
EA952SA-243	24	3	18.9
EA952SA-244	24	3.5	32.6
EA952SA-245	24	4	48.3
EA952SA-261	26	3	18.8
EA952SA-262	26	3.5	32.3
EA952SA-263	26	4	55.1
EA952SA-281	28	2.3	8.2
EA952SA-282	28	3.5	32.9
EA952SA-301	30	2.3	7.8
EA952SA-302	30	3.5	29.3
EA952SA-303	30	4	46.8
EA952SA-321	32	3.5	21.7
EA952SA-322	32	4	33.7
EA952SA-351	35	3.5	19.9
EA952SA-352	35	4	29.0
EA952SA-401	40	4	26.0

※許容荷重は1mで使用された場合の数値です。

- 材質…バネ鋼
- メッキなし
- 長さ…1m