


[ステンレス製]割ピン
EA949PE-101~506



●材質…ステンレス

品番	呼び	サイズ(mm)					入数 (個)	重量(g) (1個)
		L	d	D	A	H		
EA949PE-101	1	10	0.60	1.80	3.00	1.60	19	0.07
EA949PE-102		15					18	0.10
EA949PE-103		25					15	0.15
EA949PE-104		30					13	0.16
EA949PE-121	1.2	10	1.00	2.00	3.00	2.50	19	0.09
EA949PE-122		15					18	0.12
EA949PE-123		20					16	0.15
EA949PE-124		25					14	0.18
EA949PE-125	30	13	0.21					
EA949PE-161	1.6	10	1.40	2.80	3.20	2.50	18	0.18
EA949PE-162		15					16	0.24
EA949PE-163		20					14	0.30
EA949PE-164		25					12	0.36
EA949PE-165		30					11	0.42
EA949PE-166		35					10	0.47
EA949PE-167	40	9	0.54					
EA949PE-201	2	10	1.80	3.60	4.00	2.50	14	0.30
EA949PE-202		15					13	0.40
EA949PE-203		20					12	0.50
EA949PE-204		25					11	0.60
EA949PE-205		30					9	0.70
EA949PE-206		35					8	0.80
EA949PE-207	40	7	0.90					
EA949PE-251	2.5	15	2.30	4.60	5.00	2.50	10	0.69
EA949PE-252		20					9	0.85
EA949PE-253		25					8	1.01
EA949PE-254		30					7	1.18
EA949PE-255		35						1.34
EA949PE-256		40					6	1.50
EA949PE-257	50	5	1.83					

品番	呼び	サイズ(mm)					入数 (個)	重量(g) (1個)
		L	d	D	A	H		
EA949PE-301	3	15	2.80	5.60	6.00	3.20	9	1.14
EA949PE-302		20					8	1.40
EA949PE-303		25					7	1.66
EA949PE-304		30					6	1.92
EA949PE-305		35					5	2.18
EA949PE-306		40						2.44
EA949PE-307		50					4	2.96
EA949PE-351	3.5	15	3.30	6.60	7.00	3.20	4	2.03
EA949PE-352		20					2.45	
EA949PE-353		25					3	2.87
EA949PE-354		30						3.29
EA949PE-355		35						3.71
EA949PE-356		40					4.14	
EA949PE-357		45					2	4.56
EA949PE-358		50					4.98	
EA949PE-401	4	20	3.70	7.40	8.00	4.00	5	2.45
EA949PE-402		25					4	2.87
EA949PE-403		30						3.29
EA949PE-404		35						3.71
EA949PE-405		40					3	4.14
EA949PE-406		45						4.56
EA949PE-407		50						4.98
EA949PE-451	4.5	25	4.10	8.20	9.00	4.00	3	4.70
EA949PE-452		30						5.35
EA949PE-453		40						6.65
EA949PE-454		45					7.31	
EA949PE-455		50					2	8.09
EA949PE-501	5	25	4.60	9.20	10.00	4.00	3	4.70
EA949PE-502		30						5.35
EA949PE-503		35					2	6.00
EA949PE-504		40						6.65
EA949PE-505		45						7.31
EA949PE-506		50						8.09