

メーカー型式	品番	メトリック		UNC	
		サイズ	下穴サイズ(mm)	サイズ	下穴サイズ(mm)
50089-17	EA949VC-3A	M3	3.3	5-40	3.4
50125-13	EA949VC-4A	M4-0.7	4.3	8-32	4.4
50140-11	EA949VC-4.5A			10-24	5.1
50156-9	EA949VC-5A	M5-0.8	5.3	12-24	5.8
50188-5	EA949VC-6A	M6-1.0	6.3		
50219-4	EA949VC-7A	M7-1.0	7.3	5/16-18	8.3
50250-7	EA949VC-8A	M8-1.0・1.25	8.3		
50281-5	EA949VC-10A	M9-1.0/M10-1.5	9.3/10.3		
50344-4	EA949VC-10BA	M10-1.0・1.25	10.3		
50375-1	EA949VC-11A	M11-1.0・1.25・1.5	11.3		
50438-0	EA949VC-12A	M12・M13全ピッチ	12.3・13.3		
50468-0	EA949VC-14A	M14-1.5・2.0/M15	14.3/15.3		
50500-0	EA949VC-16A	M16-1.5・2.0	16.3	5/8-11	16.5
33588	EA949VG-1A			8-32	4.4
33608	EA949VG-2A			10-24	5.1
33628	EA949VG-3A			12-24	5.8
33048	EA949VG-4A			1/4-20	6.7
33058	EA949VG-5A			5/16-18	8.3
33068	EA949VG-6A			3/8-16	9.9
33078	EA949VG-7A			7/16-14	11.5
33088	EA949VG-8A			1/2-13	13
33108	EA949VG-9A			5/8-11	16.5
34588	EA949VH-1A				
34608	EA949VH-2A				
34628	EA949VH-3A				
34048	EA949VH-4A				
34058	EA949VH-5A				
34068	EA949VH-6A				
34078	EA949VH-7A				
34088	EA949VH-8A				
34108	EA949VH-9A				
23583	EA949VG-11			8-32	4.4
23603	EA949VG-12			10-24	5.1
23623	EA949VG-13			12-24	5.8
23043	EA949VG-14			1/4-20	6.7
23053	EA949VG-15			5/16-18	8.3
23063	EA949VG-16			3/8-16	9.9
23073	EA949VG-17			7/16-14	11.5
23083	EA949VG-18			1/2-13	13
23103	EA949VG-19			5/8-13	16.5
24583	EA949VH-11				
24603	EA949VH-12				
24623	EA949VH-13				
24043	EA949VH-14				
24053	EA949VH-15				
24063	EA949VH-16				
24073	EA949VH-17				
24083	EA949VH-18				
24103	EA949VH-19				

メーカー型式	品番	UNF		BSW	
		サイズ	下穴サイズ(mm)	サイズ	下穴サイズ(mm)
50089-17	EA949VC-3A			1/8-40	3.4
50125-13	EA949VC-4A	8-36	4.4		
50140-11	EA949VC-4.5A			3/16-24	5
50156-9	EA949VC-5A	10-32	5.1		
50188-5	EA949VC-6A			1/4-20	6.7
50219-4	EA949VC-7A				
50250-7	EA949VC-8A	5/16-24	8.2		
50281-5	EA949VC-10A				
50344-4	EA949VC-10BA	3/8-24	9.8		
50375-1	EA949VC-11A	7/16-20	11.5		
50438-0	EA949VC-12A			1/2-12	13
50468-0	EA949VC-14A				
50500-0	EA949VC-16A				
33588	EA949VG-1A				
33608	EA949VG-2A				
33628	EA949VG-3A				
33048	EA949VG-4A				
33058	EA949VG-5A				
33068	EA949VG-6A				
33078	EA949VG-7A				
33088	EA949VG-8A				
33108	EA949VG-9A				
34588	EA949VH-1A	8-36	4.4		
34608	EA949VH-2A	10-32	5.1		
34628	EA949VH-3A	12-28	5.8		
34048	EA949VH-4A	1/4-28	6.6		
34058	EA949VH-5A	5/16-24	8.2		
34068	EA949VH-6A	3/8-24	9.8		
34078	EA949VH-7A	7/16-20	11.5		
34088	EA949VH-8A	1/2-20	13		
34108	EA949VH-9A	5/8-18	16.3		
23583	EA949VG-11				
23603	EA949VG-12				
23623	EA949VG-13				
23043	EA949VG-14				
23053	EA949VG-15				
23063	EA949VG-16				
23073	EA949VG-17				
23083	EA949VG-18				
23103	EA949VG-19				
24583	EA949VH-11	8-36	4.4		
24603	EA949VH-12	10-32	5.1		
24623	EA949VH-13	12-28	5.8		
24043	EA949VH-14	1/4-28	6.6		
24053	EA949VH-15	5/16-24	8.2		
24063	EA949VH-16	3/8-24	9.8		
24073	EA949VH-17	7/16-20	11.5		
24083	EA949VH-18	1/2-20	13		
24103	EA949VH-19	5/8-18	16.3		

メーカー型式	品番	BSF		CUMMINS HEAD BOLT	
		サイズ	下穴サイズ(mm)	サイズ	下穴サイズ(mm)
50089-17	EA949VC-3A				
50125-13	EA949VC-4A				
50140-11	EA949VC-4.5A				
50156-9	EA949VC-5A	3/16-32	5		
50188-5	EA949VC-6A				
50219-4	EA949VC-7A				
50250-7	EA949VC-8A				
50281-5	EA949VC-10A	3/8-20	9.8		
50344-4	EA949VC-10BA				
50375-1	EA949VC-11A	7/16-18	11.5		
50438-0	EA949VC-12A	1/2-16	13		
50468-0	EA949VC-14A	9/16-16	14.5		
50500-0	EA949VC-16A			11/16-16	18
33588	EA949VG-1A				
33608	EA949VG-2A				
33628	EA949VG-3A				
33048	EA949VG-4A				
33058	EA949VG-5A				
33068	EA949VG-6A				
33078	EA949VG-7A				
33088	EA949VG-8A				
33108	EA949VG-9A				
34588	EA949VH-1A				
34608	EA949VH-2A				
34628	EA949VH-3A				
34048	EA949VH-4A				
34058	EA949VH-5A				
34068	EA949VH-6A				
34078	EA949VH-7A				
34088	EA949VH-8A				
34108	EA949VH-9A				
23583	EA949VG-11				
23603	EA949VG-12				
23623	EA949VG-13				
23043	EA949VG-14				
23053	EA949VG-15				
23063	EA949VG-16				
23073	EA949VG-17				
23083	EA949VG-18				
23103	EA949VG-19				
24583	EA949VH-11				
24603	EA949VH-12				
24623	EA949VH-13				
24043	EA949VH-14				
24053	EA949VH-15				
24063	EA949VH-16				
24073	EA949VH-17				
24083	EA949VH-18				
24103	EA949VH-19				