



NO	PART NAME	RAW MAT'L	Q'TY
1	FRONT COVER	PP	1
2	BACK COVER	PP	1
3	PCB ASS'Y	CEM	1
4	TOGGLE SWITCH		1
5	LED LAMP	φ3,RED	1
6	WATERPROOF CAP		1
7	CONNECTER WIRE		1
8	CONNECTER PIN		2
9	SCREW	M4x10	9
10	SCREW	M2x6	2
11	BODY PACKING	NBR	1
12	BODY	POM	1
13	O-RING(BODY)	NBR	1
14	DRUM BUNG ADAPTER	PP	1
15	LOCK NUT	PP	1
16	STAINLESS STEEL INNER PIPE	STAINLESS STEEL(SUS 304)	1
17	SUCTION PIPE(INNER)	PE	1
18	O-RING(SUCTION PIPE(INNER), MOTOR COVER)	NBR	3
19	JOINT NUT(PIPE)	PP	1
20	O-RING(PIPE)	NBR	1
21	SUCTION PIPE(OUTER)	PE	1
22	MOTOR WIRE	URETHANE	1
23	MOTOR COVER PACKING	NBR	1
24	MOTOR COVER	POM	1
25	O-RING(MOTOR COVER TOP)	NBR	1
26	O-RING(MOTOR)	NBR	1
27	MOTOR		1
28	MOTOR PACKING	NBR	1
29	MOTOR CASE	POM	1
30	IMPELLER	POM	1
31	IMPELLER CASING	POM	1
32	FILTER	STAINLESS STEEL(SUS 304)	1
33	END CAP	POM	1
34	O-RING(HOSE ADAPTER, SPOUT)	NBR	3
35	HOSE ADAPTER	PP	2
36	JOINT NUT(HOSE ADAPTER, SPOUT)	PP	3
37	HOSE CLAMP	STAINLESS STEEL(SUS 304)	2
38	DISCHARGE HOSE	FLEXIBLE MULTI-LAYER PVC	1
39	HANDLE	PP	1
40	NOZZLE CAP	PP	1
41	O-RING(NOZZLE CAP)	NBR	1
42	NOZZLE SPRING	STAINLESS STEEL(SUS 304)	1
43	NOZZLE PISTON	POM	1
44	O-RING(PISTON L)	NBR	1
45	O-RING(PISTON S)	NBR	1
46	NOZZLE HOOK	PP	1
47	SPOUT	PP	1
48	NOZZLE LEVER	PP	1
49	RIVET	ALUMINUM	1

UNIT	M/M	MAT'L	-	PART NAME	ASSEMBLY	DATE	2018.7.6
SCALE	NS	ANGLE	⊕	DWG NO.			
TITLE:	ELECTRIC DRUM PUMP			MODEL NO.	DEP-1702		
DESIGNED BY	CHECKED BY	APPROVED BY	Dukshin Corp., Ltd.				
LEE E K							