


EA116SD

2HP DIRECTLY DRIVEN COMPRESSOR W/30L. TANK

2015/1/5



PARTS LIST

No.	Parts No.	Description	Q'ty
1	SD2030-01	Cylinder Head	1
2	SD2030-02	Cylinder Head Packing	1
3	SD2030-03	Inlet Valve Seat	1
4	SD2030-04	Inlet & Exhaust Valve Seat Packing	1
5	SD2030-05	Inlet & Exhaust Valve Plate	2
6	SD2030-06	Inlet & Exhaust Spring Plate	2
8	SD2030-08	Pin	4
9	SD2030-09	In Six-Angle Bolt	4
10	SD2030-10	Spring Washer	4
11	SD2030-11	Exhaust Elbow	1
12S	SD2030-12S	Exhaust Tube Set	1
13	SD2030-13	Quick Coupler	1
14	SD2030-14	Exhaust Valve Seat	1
15	SD2030-15	Valve Seat Packing	1
16	SD2030-16	Cylinder	1
17	SD2030-17	Piston	1
18	SD2030-18	Compression Ring	2
19	SD2030-19	Oil Control Ring	1
20	SD2030-20	Piston Pin	1
21	SD2030-21	Piston Pin Snap Ring	2
22	SD2030-22	Cylinder Packing	1
23	SD2030-23	Set Nut	2
24	SD2030-24	Spring Washer	2
25	SD2030-25	Double Head Screw	2
26	SD2030-26	Crankcase	1
27	SD2030-27	Front Cover Packing	1
28	SD2030-28	Crankshaft	1
29	SD2030-29	Front Cover	1
30	SD2030-30	Rod	1
31	SD2030-31	Oil Gauge	1
32	SD2030-32	Oil Draining Plug	1
33	SD2030-33	Motor Cover	1
34	SD2030-34	In Six-Angle Bolt	9
35B	SD2030-35B	Air Filter	1
36	SD2030-36	Air Flue Oil Filling Assembly	1
37	SD2030-37	Motor	1
38	SD2030-38	Radiation Fan	1
39	SD2030-39	Oil Gauge Packing	1
40	SD2030-40	Air Tank	1
41	SD2030-41	Pressure Gauge	1
42	SD2030-42	Regulator Valve	1
43	SD2030-43	Rubber Handle	1
44	SD2030-44	Tank Wheel Nut	2
45	SD2030-45	Tank Wheel	2
46	SD2030-46	Tank Feet Rubber Packing	2
47	SD2030-47	Drain Cock	1
48	SD2030-48	Check Valve	1
49	SD2030-49	Pressure Gauge	1
50	SD2030-50	Pressure Switch	1
51	SD2030-51	Nipple	1
52	SD2030-52	Unloading Tube A'ssy	1
53	SD2030-53	Unloading Elbow	1
54	SD2030-54	Cable Wire	1
55	SD2030-55	Power Wire	1
56	SD2030-56	Safety Valve	1
57	SD2030-57	Plate Washer	2
58	SD2030-58	Circuit Breaker	1
59	SD2030-59	Round-Head Bolt	2
60	SD2030-60	Plate Washer	2
61	SD2030-61	Strain Relief Clip	1
62	SD2030-62	Spring Washer	4
64	SD2030-64	Run Capacitor	1
65	SD2030-65	Capacitor Cover	1
66	SD2030-66	Centrifugal Switch	1
67	SD2030-67	Start Capacitor	1
68	SD2030-68	Air Filter (Element Only)	1

SD2030-50/60-P-1409H-VO