

品番：EA538NM

品名：圧着端子セット



販売価格	7,900円(税抜) / 8,690円(税込)		
カタログ価格	7,900円(税抜) / 8,690円(税込)		
在庫数	最新在庫: 0 (2026/03/25 20:46現在)		
商品入数	1	販売単位	St
カタログページ			



仕様

セット内容	絶縁丸端子(赤):V1.25-3(10個) 絶縁丸端子(赤):V1.25-4(10個) 絶縁丸端子(青):V2-3(10個) 絶縁丸端子(青):V2-4(10個) 絶縁丸端子(青):V2-5(10個) 絶縁丸端子(黄):V5.5-4(5個) 絶縁丸端子(黄):V5.5-5(5個) 絶縁丸端子(黄):V5.5-6(5個) 閉端接続子:CE 1(10個) 閉端接続子:CE 2(10個) 閉端接続子:CE 5(5個) 閉端接続子:CE 8(5個) 赤絶縁スリーブ:VB-1.25(10個) 青絶縁スリーブ:VB-2(10個) 黄絶縁スリーブ:VB-5.5(5個) 絶縁Y型赤圧着端子:V1.25-YAS3 (10個) 絶縁Y型赤圧着端子:V1.25-YAS4 (10個) 絶縁Y型青圧着端子:V2-YAS3(10 個) 絶縁Y型青圧着端子:V2-YAS4(10 個) 裸丸型圧着端子:R1.25-4(10個) 裸丸型圧着端子:R1.25-5(10個) 裸丸型圧着端子:R2-3(10個) 裸丸型圧着端子:R2-4(10個)	ケースサイズ	245(W)×190(D)×40(H)mm
-------	--	--------	-----------------------

	裸丸型圧着端子:R2-5(10個) 裸丸型圧着端子:R3.5-4(5個) 裸丸型圧着端子:R5.5-5(5個) 裸丸型圧着端子:R5.5-8(5個) 裸丸型圧着端子:R8-8(5個) 裸丸型圧着端子:R22-10(5個) 裸丸型圧着端子:R38-10(3個) 裸Y型圧着端子:1.25-YAS3(10個) 裸Y型圧着端子:2-YAS4(10個) 赤ピン端子(雄):09F(5個) 赤ピン端子(雌):09M(5個) 青ピン端子(雄):20F(5個) 青ピン端子(雌):20M(5個)	
総重量	780g	

株式会社エスコ

大阪府大阪市西区立売堀3丁目8番14号 06-6532-6226(代表)

© 2018 ESCO Co.,Ltd.