


# ポリエステルスリング

EA981TA-0.5~10、TB-0.5~10、TC-1.5~10  
 TD-0.5~10、RK-1.5~10、RL-1.5~10



- 材質…ポリエステル
- 表面は青色ですが、芯材は白色です。  
 芯材の白色が見えたら寿命ですので品質管理に有効です。




品番	揚量	全長 (m)	アイ長さ (mm)	アイ(mm)		縫製部(mm)		本体(mm)	
				幅	太さ	幅	太さ	幅	太さ
EA981TA-0.5	(幅)25mm (0.8t)	0.5	150	27	6	25	12	25	8
EA981TA-1									
EA981TA-1.5									
EA981TA-2									
EA981TA-2.5									
EA981TA-3									
EA981TA-3.5									
EA981TA-4									
EA981TA-5									
EA981TA-6									
EA981TA-8									
<del>EA981TA-10</del>	(幅)35mm (1.25t)	0.5	150	37	6	35	12	35	8
EA981TD-0.5									
EA981TD-1									
EA981TD-1.5									
EA981TD-2									
EA981TD-2.5									
EA981TD-3									
EA981TD-3.5									
EA981TD-4									
EA981TD-5									
EA981TD-6									
EA981TD-7									
EA981TD-8									
EA981TD-9									
EA981TD-10									
<del>EA981TB-0.5</del>	(幅)50mm (1.6t)	0.5	150	27	14	50	12	50	8
EA981TB-1									
EA981TB-1.5									
EA981TB-2									
EA981TB-2.5									
EA981TB-3									
EA981TB-3.5									
EA981TB-4									
EA981TB-5									
EA981TB-6									
EA981TB-8									
EA981TB-10									

取扱中止

取扱中止

取扱中止



品番	揚量	全長 (m)	アイ長さ (mm)	アイ(mm)		縫製部(mm)		本体(mm)	
				幅	太さ	幅	太さ	幅	太さ
EA981TC-1.5	(幅)75mm (2.5t)	1.5	400	40	14	75	12	75	8
EA981TC-2		2.0							
EA981TC-2.5		2.5							
EA981TC-3		3.0							
EA981TC-4		4.0							
EA981TC-5		5.0							
EA981TC-6		6.0							
EA981TC-8		8.0							
EA981TC-10		10.0							
<del>EA981RK-1.5</del>		(幅)100mm (3.2t)							
<del>EA981RK-2</del>	2.0								
<del>EA981RK-2.5</del>	2.5								
<del>EA981RK-3</del>	3.0								
<del>EA981RK-4</del>	4.0								
<del>EA981RK-5</del>	5.0								
<del>EA981RK-6</del>	6.0								
<del>EA981RK-8</del>	8.0								
<del>EA981RK-10</del>	10.0								
<del>EA981RL-1.5</del>	(幅)150mm (5.0t)		1.5	500	55	18	150	12	150
<del>EA981RL-2</del>		2.0							
<del>EA981RL-2.5</del>		2.5							
<del>EA981RL-3</del>		3.0							
<del>EA981RL-4</del>		4.0							
<del>EA981RL-5</del>		5.0							
<del>EA981RL-6</del>		6.0							
<del>EA981RL-8</del>		8.0							
<del>EA981RL-10</del>		10.0							

~~取扱中止~~  
~~取扱中止~~  
~~取扱中止~~  
~~取扱中止~~  
~~取扱中止~~  
~~取扱中止~~  
~~取扱中止~~  
~~取扱中止~~  
~~取扱中止~~  
~~取扱中止~~  
~~取扱中止~~  
~~取扱中止~~  
~~取扱中止~~  
~~取扱中止~~  
~~取扱中止~~  
~~取扱中止~~  
~~取扱中止~~  
~~取扱中止~~  
~~取扱中止~~  
~~取扱中止~~  
~~取扱中止~~

21.Jul.