

# LET OTC HANDLE THE HEAVY WORK



**EA993RC**

## 5090 BACK BUDDY™ II

- Remove, transport, service, and install heavy truck brake drums and hub assemblies.
- Fast-motion ratcheting jack with 14" of vertical lift.
- Pneumatic rear tires.
- Tilting mechanism to achieve the exact angle necessary for precise reassembly.
- Fold-down handle for open access to the work area.
- Onboard lube tray and toolbox.
- An array of optional adapter sets capable of grabbing almost any truck hub assembly or brake drum, inboard or outboard.

### Adapter Sets (sold separately)

**513926** – 10 stud inboard hub & drum assemblies – 335 mm.

**513927** – 10 hole outboard drums – 3/4" thick back plates

**513925** – 5 and 6 spoke wheels

**514644** – 8 stud inboard hub & drum assemblies

**514645** – 8 hole outboard drums

**514646** – 6 stud inboard hub & drum assemblies

**514647** – 6 hole outboard drums

**514648** – Humvee/Hummer geared hubs



16-04

EA993RE

## 5100 WHEEL MATE™

The Wheel Mate enables truck mechanics to easily remove, install, rotate, and transport single tire/wheel assemblies. Its features include:

- Internal ratcheting jack with 14 inches of vertical travel – almost a foot higher than conventional dollies.
- U-shaped chassis that provides close, unhindered access to work area.
- A design that accommodates –and securely holds – almost any truck wheel, including wide-based singles, without restraining chains.
- Heavy-duty ball bearing wheels mounted under ball bearing swivel casters for maximum maneuverability.
- Rugged structural steel tubing construction that meets the demands of the toughest shop environments.
- Foot-operated wheel lock.



Wheel Mate is ideal for tire inspection, repair, and maintenance operations.

## 5095A & 5096A EASY LEVER WHEEL DOLLIES

These wheel dollies give mechanics the leverage they need to easily remove or install truck tire-and-wheel assemblies. Its features include:

- Heavy-duty construction capable of toting 300 pounds.
- Onboard rollers that make stud hole alignment a snap.
- Spring-loaded kickstand for handy parking.
- Rugged tubular-steel construction.
- Two models that, together, can accommodate tire diameters from 24 to 48 inches.

**No. 5095A** – Easy Lever Wheel Dolly (light/medium tire dia. 24" to 36")

**No. 5096A** – HD Easy Lever Wheel Dolly (heavy-duty tire dia. 36" to 48")



Clever Lever's easy lift and pull action removes the tire. Inside wheels pull off just as easy.