


No.12 ホース継手

(Rネジ)



規格	ネジD	d	d1	L	L1	L2	六角対辺
No.12×1/8(N)	R1/8	6.8	4	33	20	8	10
No.12×1/4(N)	R1/4	8.7	5	42	25	11	14
No.12×3/8(N)	R3/8	11	6	49	30	12	17
No.12×1/2(N)	R1/2	14.5	9.5	59	35	15	22
No.12×3/4(N)	R3/4	20.5	13	71	45	17	28
No.12×1/8×8.5(N)	R1/8	8.7	5	33	20	8	10
No.12×1/8×11(N)	R1/8	11	5.5	39	25	8	14
No.12×1/4×7(N)	R1/4	6.8	4	37	20	11	14
No.12×1/4×11(N)	R1/4	11	6	42	25	11	14
No.12×1/4×12.7(N)	R1/4	12.7	7.5	47.5	30	11	14
No.12×3/8×7(N)	R3/8	6.8	4	39	20	12	17
No.12×3/8×8.5(N)	R3/8	8.7	5	44	25	12	17
No.12×3/8×12.7(N)	R3/8	12.7	7.5	49	30	12	17
No.12×3/8×14.5(N)	R3/8	14.5	9	54	35	12	17
No.12×1/2×8.5(N)	R1/2	8.7	5	49	25	15	22
No.12×1/2×11(N)	R1/2	11	6	54	30	15	22
No.12×1/2×12.7(N)	R1/2	12.7	7.5	54	30	15	22
No.12×1/2×17.5(N)	R1/2	17.5	11.5	59	35	15	22
No.12×1/2×20.5(N)	R1/2	20.5	13	66	42	15	22
No.12×3/4×14.5(N)	R3/4	14.5	9.5	61	35	17	28
※No.12×1"	R1"	28	20	74	45	19	36

※No.12×1" はメッキ無のみとなっております。