



A CONTRACTOR'S BEST FRIEND



U.S. PATENT NO. D767,846



FEATURES

- Heavy-duty roll cage construction
- Ultra compact design
- Chain drive
- Interchangeable cleaning tools
- Quick connect threadless shaft manifold
- "Sweet Spot" 862.5 rpm
- Simultaneous water flush
- Foot switch activation
- Reversible shaft rotation



RAM PRO® – Rugged and Dependable

Tackle demanding commercial tube cleaning environments with the powerful RAM PRO—engineered for contractors. Not only is this compact unit half the weight of other tube cleaners, it's also designed to save time. A sturdy roll cage provides protection both on the job and inside a crowded work truck. Vibration isolators connect to the motor assembly to help tolerate bumps and jolts. The Quick Connect shaft attaches with a firm push, allowing for fast setup and easy breakdown and transportation. The performance drive system replaces traditional rubber belts with a metal chain drive. No more slipping belts!

RAM-PRO-60: Compact tube cleaner, including roll cage, quick connect shaft manifold and two-direction foot switch
(115V 50/60 Hz) **Call for Price**

RAM PRO	
Motor Power	0.25 HP (115V units) 0.5 HP (230V units)
Input Power	Standard: 5.5 amps, 115V, 60 Hz AC Optional: 5.5 amps, 115V, 50 Hz; 4.5 amps, 230V, 60 Hz; or 4.5 amps, 230V, 50 Hz
Power Supply Cord	12', 18-3 GFCI
Flexible Shaft Speed	862.5 rpm
Water Requirements	Minimum 30 PSI at 2 GPM
Dimensions	16" high x 9" wide x 20" deep
Weight	34 lbs net dry

GOODWAY®
INNOVATIVE MAINTENANCE SOLUTIONS

Call: 1-800-333-7467

Visit: www.goodway.com

Goodway Technologies Corporation

420 West Avenue, Stamford, CT 06902-6384 U.S.A.

Phone: 203-359-4708 • Fax: 203-359-9601 • goodway@goodway.com