



New



PTFE-o-Seal

Dynamic Thread Sealing



Characteristics PTFE-o-Seal:

- suitable for almost all metal or plastic threads
- seals directly, no additional additives are required
- adapts automatically to the form of the thread
- easy to use
- resistant to a variety of aggressive media
- not flammable, does not melt and does not dissolve, almost indestructible
- durable for an unlimited period of time
- neutral against water and oxygen
- DVGW-approval for up to 100 bar for gases
- approved for liquid and gaseous oxygen
- tested with 45° back-twist
- temperature resistant from -200°C up to +240°C

The number of wraps must be adjusted to the size of the pipe diameter.*

* Examples

1/2" 12 (fine threads) or 18 (course threads) wraps
1 1/2" 16 (fine threads) or 24 (course threads) wraps

For easier assembling of the Dynamic Thread Sealing, apply WEICON PTFE-o-Seal Assembling and Lubrication Agent generously.

Characteristics

WEICON PTFE-o-Seal

Assembling and Lubrication Agent:

- facilitates the assembling
- increases the sliding ability



Packaging:

Set Art.-No.: 30001000

WEICON GmbH & Co. KG
(Headquarter)
Königsberger Str. 255 · DE-48157 Münster
P.O. Box 84 60 · DE-48045 Münster
Germany

Tel. +49 (0) 251 / 93 22-0
Fax +49 (0) 251 / 93 22-244
Fax +49 (0) 251 / 93 22-233 Export
www.weicon.de · info@weicon.de

WEICON Middle East L.L.C.
Jebel Ali Ind Area 3 · P.O. Box 118 216
Dubai · U.A.E

Phone +971 4 880 25 05
Fax +971 4 880 25 09
Mobile +971 50 545 99 83
www.weicon.ae · info@weicon.ae

WEICON Inc.
20 Steckle Place · Unit 20
Kitchener · Ontario · N2E 2C3
Canada
Phone +1 519 896 5252
Fax +1 519 896 5254
Cell +1 519 590 5168
www.weicon.ca · info@weicon.ca

WEICON Kimya Sanayi Tic. Ltd. Şti.
Yenibosna Mahallesi Yalçın Koreş Caddesi
Arifağa Sokak No: 29 Kat: 3
34530 Yenibosna – Istanbul Turkey
www.weicon.biz.tr · info@weicon.biz.tr

WEICON Romania SRL
Str. Depozitelor 22
540240 Targu Mures, jud. Mures Romania
www.weicon.com · office@weicon.com



Distributed by:



Any product specifications and recommendations given herein must not be seen as guaranteed product characteristics. They are based on our laboratory tests and on practical experience. Since individual application conditions are beyond our knowledge, control and responsibility, this information is provided without any obligation. We do warrant the continuously high quality of our products being free from defects in accordance with and subject to our General Sales Conditions. However, own adequate laboratory and practical tests to find out if the product in question meets the requested properties are recommended. A claim cannot be derived from them. The user bears the only responsibility for non-appropriate or other than specified applications.