



**MCR**  
**SAFETY**

# 9365

## Cut Protection Specification Sheet

### PRODUCT DESCRIPTION:

Kevlar® string knit gloves are used for general purpose work applications to provide cut and abrasion resistance, using high performance yarns, to further protect the hands when working with sharp objects. The 9365 features 100 percent Kevlar® regular weight fibers that is dotted on one side with black PVC dots.

### FEATURES:

- DuPont™ Kevlar® brand fiber
- High comfort level
- Allows manual dexterity
- Certified by DuPont™ as a licensed glove manufacturer
- Launderable

### APPLICATIONS:

Manufacturing, Food service, Glass handling, HVAC,  
Warehousing




### TECHNICAL DATA FOR: 9365

**Material Group**  
**Product Type**  
**Glove Size**  
**Gauge**  
**Material**

Strings  
Cut Protection  
Large  
7 Gauge  
Kevlar

**ANSI Cut**  
**ANSI Abrasion**  
**ANSI Puncture**

ANSI Cut A3  
ANSI Abrasion 2  
ANSI Puncture 2



| Item No: | Size: | A: | B: | C: | Case Weight | UOM Weight |
|----------|-------|----|----|----|-------------|------------|
|----------|-------|----|----|----|-------------|------------|

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2017 MCR Safety - All Rights Reserved



**MCR**  
**SAFETY**

# 9365

## Cut Protection Specification Sheet

| Item No: | Size:     | A:     | B:    | C:  |            |
|----------|-----------|--------|-------|-----|------------|
| 9365L    | Large     | 9.750  | 4.375 | N/A | EA354E-12B |
| 9365M    | Medium    | 9.438  | 4.375 | N/A | EA354E-12A |
| 9365S    | Small     | 9.500  | 4.064 | N/A |            |
| 9365XL   | X - Large | 10.750 | 4.875 | N/A |            |

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2017 MCR Safety - All Rights Reserved