


EA423R-11-50 フッ素ゴムオーリング(5個入り)



《形状・寸法》



	内径(d1)		太さ(d2)の基準寸法と許容差		溝部の寸法(参考)	
	基準寸法	許容差	2.4±0.09	3.5±0.10	軸径	穴径
			呼び番号			
EA423R-11	10.8	±0.18	P11		11	15
EA423R-12	11.8	±0.19	P12		12	16
EA423R-14	13.8	±0.19	P14		14	18
EA423R-15	14.8	±0.2	P15		15	19
EA423R-16	15.8	±0.2	P16		16	20
EA423R-18	17.8	±0.21	P18		18	22
EA423R-20	19.8	±0.22	P20		20	24
EA423R-21	20.8	±0.23	P21		21	25
EA423R-22	21.8	±0.24	P22		22	26
EA423R-24	23.7	±0.24		P24	24	30
EA423R-25	24.7	±0.25		P25	25	31
EA423R-26	25.7	±0.26		P26	26	32
EA423R-28	27.7	±0.16		P28	28	34
EA423R-29	28.7	±0.28		P29	29	35
EA423R-30	29.7	±0.29		P30	30	36
EA423R-32	31.7	±0.31		P32	32	38
EA423R-34	33.7	±0.33		P34	34	40
EA423R-35	34.7	±0.34		P35	35	41
EA423R-36	35.7	±0.34		P36	36	42
EA423R-38	37.7	±0.37		P38	38	44
EA423R-39	38.7	±0.37		P39	39	45
EA423R-40	39.7	±0.37		P40	40	46
EA423R-42	31.7	±0.39		P42	42	48
EA423R-44	43.7	±0.41		P44	44	50
EA423R-45	44.7	±0.41		P45	45	51
EA423R-46	45.7	±0.42		P46	46	52
EA423R-48	47.7	±0.44		P48	48	54
EA423R-49	48.7	±0.45		P49	49	55
EA423R-50	49.7	±0.45		P50	50	56