

Drill Press Vices Unigrip

DPVUG DPV3UG

Low profile & compact vices are suitable for use with drill stands, bench drills and drill presses in metal and woodworking applications

Graded cast iron construction with precision ground base and vice bed

Fixed jaw with 3 longitudinal and 1 transversal prisms for firm gripping of round stock both horizontally and vertically


Special seat in jaws for clamping of low height work pieces

Spindle moves inside the hollow hand grip making the vice usable on any position across the table Elongated clamping slots for rapid adjustment of the vice on the work table help save time



3 Way Drill Press Vice

3 mounting options useful drilling along all axes with a single setting of the job and holding of long workpieces which are cumbersome and difficult to manage in regular vices





Fully ground side face allows for right angle machining with the same jaw setting. The jaw width acts as jaw height facilitating longer workpieces to be held

Fully ground end face allows for right angle machining with the same machine setting



ORDERING INFORMATION

CAT NR.	ORD NR.	JAW WIDTH		JAW OPENING		JAW DEPTH		BOX
		(INCH)	(MM)	(INCH)	(MM)	(INCH)	(MM)	QTY.
DRILL PRESS VIC	ES - UNIGRIP					,		
DPV/UG/75	35120	3-3/16	80	2-3/4	70	1-3/16	30	6
★ DPV/UG/100	35121	4	100	3-5/8	92	1-3/16	30	4
★ DPV/UG/125	35122	5	120	4-3/8	110	1-3/8	35	3
3 WAY DRILL PRE	SS VICE - UN	IGRIP		•		,		
DPV/UG/3/100	35125	4	100	3-1/2	88	1-3/16	30	4