


EA423R-3-10 フッ素ゴムオーリング(10個入り)



《形状・寸法》



単位 : mm

	内径(d1)		太さ(d2)の基準 寸法と許容差	溝部の寸法 (参考)	
	基準寸法	許容差	1.9 ± 0.08	軸径	穴径
			呼び番号		
EA423R-3	2.8	± 0.14	P3	3	6
EA423R-4	3.8	± 0.14	P4	4	7
EA423R-5	4.8	± 0.15	P5	5	8
EA423R-6	5.8	± 0.15	P6	6	9
EA423R-7	6.8	± 0.16	P7	7	10
EA423R-8	7.8	± 0.16	P8	8	11
EA423R-9	8.8	± 0.17	P9	9	12
EA423R-10	9.8	± 0.17	P10	10	13

耐熱温度・・・150