


EA584AA-1~-3、A-6A~-12A

(エキストラクター単品)


- ダメージを受けたネジヘッド抜き取り工具
- 工具鋼製
- 電動ドリルと併用します。
電動ドリルは左回転(反時計方向)のみで使用してください。

EA584AA-1~-3




Removes these types of screws

EA584A-8A~-12A




EA584A-3A~-6A




- 電動ドリルと併用してください。
電動ドリルは左回転(反時計方向)のみで使用してください。

DRILL-OUT® – Micro Power Extractor




 Ø mm	RPM (t / mn)
M3 #5, #6	75-100
M4 #8	75-100
M5 #10, #12	75-100
M6 1/4" M7	75-100




 Ø mm	RPM (t / mn)
M3 #5, #6	50
M4 #8	50
M5 #10, #12	50
M6 1/4" M7	50

DRILL-OUT® – Power Extractor



 Ø mm	RPM (t / mn)
M6 1/4" M7	700-800
5/16" M8 M9	650-750
3/8" M10 M11	600-700
M12 1/2" M13	475-575



 Ø mm	RPM (t / mn)
M6 1/4" M7	350
5/16" M8 M9	470
3/8" M10 M11	840
M12 1/2" M13	1400



EA584AA-8A~12A

	A	B	C	D	E	品番
M8	32	3.7	7	6.4	4.8	EA584A-8A
M10	37.5	4.8	8	8	6	EA584A-10A
M12	42.5	6	11	11	8	EA584A-12A (廃番)


A (単位mm)



EA584AA-3A~6A

	A	B	C	D	E	品番
M3	29	1.6	2.5	2.4	1.6	EA584A-3A
M4	32	2	3.4	3.2	2	EA584A-4A
M5	35	2.4	3.4	3.2	2.4	EA584A-5A
M6	42	3.2	4.3	4	3.2	EA584A-6A

(単位mm)



EA584AA-1~-3

ドリルナンバー	A	B	C	D	品番
NO.1	51	6.3	7	4.8	EA584AA-1 (廃番)
NO.2	51	6.3	7	—	EA584AA-2 (廃番)
NO.3	51	6.3	8	—	EA584AA-3 (廃番)

(単位mm)