

Instruction Manual

©2007 Ken-Tool

Part No. 32129-98

Industrial Wheel Lock Ring Tool Set ™ #32129

DEMOUNTING INSTRUCTIONS


If the rings are frozen together, follow steps 1-3.



Locate the gap between the ends of the split ring.



Insert the "toe" of the <u>SEPARATOR</u> end between the ends of the split ring.



Once the rings are parted, insert the "claws" of the <u>PRY-OUT</u> end behind the slotted end of the split ring.



Pry the slotted end of the split ring out and up until it is resting against the wheel flange.

These tools are designed to remove and replace lock rings on multi-piece industrial wheels. Follow Tire and Wheel Manufacturer's Instructions




Push down to separate the solid ring from the split ring.



Raise the ring until it stays in place.




Start demounting the raised end of the split ring by placing the end of the tip of the <u>DEMOUNT</u> end under the split ring.



Push down to pry up, working around the ring until it is demounted.



end under



768 E. North Street, P. O. Box 9320, Akron, Ohio 44305; Phone: 330-535-7177, Fax: 330-535-1345 www.kentool.com Contact Us: sales@kentool.com




Instruction Manual

©2007 Ken-Tool


Part No. 32129-98

Industrial Wheel Lock Ring Tool Set ™ #32129

MOUNTING INSTRUCTIONS



Start one end of the split ring in place under the wheel flange.



The first "bite" should be a <u>little</u> <u>more</u> than half way around from the started end of the split ring.



Push down...



...until the ring snaps into place.




Raise the unmounted portion of the split ring using the <u>SEPARATOR</u> end.



Pull the tool toward you to hook the <u>MOUNT</u> end under the ring.



Pull the tool toward you to hook the <u>MOUNT</u> end under the ring from the inside.



Lift up to release the tool.



Push down.

NOTE: These tools work equally well on pneumatic tires that do not require a press or cage.

768 E. North Street, P. O. Box 9320, Akron, Ohio 44305; Phone: 330-535-7177, Fax: 330-535-1345 www.kentool.com Contact Us: sales@kentool.com



Instruction Manual

©2007 Ken-Tool

Part No. Safety Warning



If you don't know how to use tire changing tools – **STOP!** Tire changing should only be done by trained persons. If you do it wrong, you could be hurt or killed.

Here are some Safety Rules. For complete tire servicing procedures, read the tire and rim makers' service manuals. You can also get free wall charts about tire servicing by calling OSHA.

USING TIRE TOOLS

ALWAYS wear eye protection when using hammers and tire irons.
ALWAYS use soft-faced hammers when driving tire irons.
NEVER use one hammer to strike another hammer.
NEVER use a hammer with a loose or cracked handle.
NEVER use a dented, cracked, chipped, or mushroomed tool.
NEVER use a tire tool for anything except mounting/demounting tires.

INFLATING TIRES

NEVER add air to a tire that has been run flat or under inflated.

NEVER hammer, strike, or pry on an inflated tire and rim.

ALWAYS use an inflation cage when inflating tires.

ALWAYS use a clip-on chuck.

ALWAYS use an extension hose with a removable valve and gauge.

NEVER inflate a tire over 40 psi if the tire beads are not seated.

NEVER use starting fluid, ether, gasoline or other flammable liquids to lubricate or seat the beads of a tubeless tire. A gigantic explosion can result.

768 E. North Street, P. O. Box 9320, Akron, Ohio 44305; Phone: 330-535-7177, Fax: 330-535-1345 Website: www.kentool.com E-Mail: sales@kentool.com