



1/ Available in 60, 92 and 135 cm versions\*

2/ Cutting carriage on 6 linear ball bearings = **smooth and precise movement**. Robust handle and sliding carriage

3/ High quality cutting wheel  $\varnothing$  22 mm in tungsten carbide titanium coated with ball bearings. Slightly different angle of attack slightly different from other castors on the market ( $120^\circ$ ) = **less effort to and does not damage the surface of mosaics**.  
Cutting accuracy : 0,3 - 0,5 mm. Hardness: 90 HRC

4/ Two different cutting separators with protection to avoid to avoid damaging the tile and allowing a maximum cutting thickness of 20 mm with less effort

5/ Lateral supports: made of aluminum, larger and adapted to the sizes of EDMATILE, to support larger tile sizes. **Graduated with adjustable and orientable stops** for easy for easy cutting, positionable along the entire length of the tile cutter

6/ Adjustable main square: made of aluminum alloy, length adapted to the different sizes of EDMATILE. **Precise graduation, laser marking. With lateral stop for repetitive straight cuts**

7/ Base: made of aluminum more than 3 mm thick. **Can support 20 mm tiles** easily, without bending

8/ **Single H-shaped guide rail**, whose straightness is adjusted by a special machine, can support a cut of up to 20 mm, and with higher cutting accuracy.



- **REF 251055 EDMATILE 600** : WITH CARRYING SOFT BAG ( STANDART CONFIGURATION )
- **REF 251001 EDMATILE 600** : **HEAVY DUTY HARD CASING BOX** ( OPTIONAL)





## **METALIC HEAVY DUTY EDMATILE STORE DISPAY.**

You can display the 3 different sizes EDMATILES as shown on picture.

You can also present 3 x EDMATILE 600 MM on it.