


Transport equipment

Product data sheet

Article no.: 9920 ESD-table top cart with trays



Electrostatic discharge construction (ESD = Electrostatic Discharge). Modular system: Steel construction, welded. Tubular steel hoop and steel plate trays screwed. Trays oil-tight, rim 40 mm high, powder coated slate grey RAL 7015. 2 swivel and 2 fixed-wheel castors. Wheels electrically conductive (anti-static) with TPE-ESD tyres (thermoplastic elastomer). Hubs with groove ball bearing. Swivel castors with wheel locks, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity of upper shelf 200 kg.

Technical Details:



Total load capacity (kg)	400
Length of usable platform (mm)	850
Width of usable platform (mm)	500
Shelf heights (mm)	207, 829
Total length (mm)	986
Total width (mm)	500
Total height (mm)	1065
Tyres	TPE-ESD
Wheel size (mm)	160 x 40
Weight (kg)	37
Country of origin	Germany
Warranty (years)	10
Customs tariff number	87168000
GTIN	4017976499208