


Standard Clamping Elements // Clamping bolts, nuts and washers



No. 6332S

**Quick-action clamping nut without collar**

hardened and zinc-plated, strength class 6.



**Accessories and Recommendations**



EA637GZ	Order no.	Size	SW	M	Weight [g]	SC	CAD
-6	<b>88146</b>	M 6	16	9,0	10		CAD
-8	<b>88534</b>	M 8	19	10,5	15		CAD
-10	<b>88559</b>	M10	22	12,5	23		CAD
-12	<b>88567</b>	M12	27	15,0	44		CAD
-16	<b>88575</b>	M16	34	16,0	68		CAD
-20	<b>88583</b>	M20	41	22,0	85		CAD

**Application:**

Slide quick-action clamping nut directly over screw thread up to clamping point and then lock it. If the quick-action clamping nut base is firmly in contact at the clamping point, then the head can be locked with the base by means of a 1/4 to 1/2 turn.

**Advantage:**

- effortless bridging of long screw thread and clamping spindles
- easy assembly/disassembly in tight and invisible spaces
- no searching for the thread
- no seizing on the thread due to outside influences
- no impaired performance through contamination such as paint residues or even rust.

