


# METRIC SHOULDER EYE BOLT

## 316-NM STAINLESS STEEL



**NOTE:**  
**MEETS ASME B30.26-2010 SECTION 26-2.0. EYE BOLTS**  
**HAVE FORGED MARKINGS OF 316-NM, SIZE AND WLL**  
**IN TONS. ALL THREADS ARE METRIC. ONE NUT AND**  
**WASHER ARE INCLUDED. EXTRA NUTS AND WASHERS**  
**ARE AVAILABLE FROM STOCK. SHAFT AND UNDERSIDE OF**  
**SHOULDER ARE MACHINED FOR PERFECT FIT AND SEATING.**

ITEM	A	B	C	D	THREAD	WLL	WT
EA638SV-	(size)					(lb)	(lb)
31 S0314-0705M	M6	1.50"	2.00"	0.50"	M6 x 1.0	500	0.06
32 S0314-0710M	M6	2.50"	4.00"	0.50"	M6 x 1.0	500	0.08
33 S0314-0803M	M8	0.38"	1.38"	0.63"	M8 x 1.25	800	0.12
34 S0314-0806M	M8	1.50"	2.25"	0.63"	M8 x 1.25	800	0.12
35 S0314-0810M	M8	2.50"	4.25"	0.63"	M8 x 1.25	800	0.14
36 S0314-1002M	M10	0.75"	0.75"	0.75"	M10 x 1.5	1,200	0.20
37 S0314-1003M	M10	1.00"	1.50"	0.75"	M10 x 1.5	1,200	0.20
38 S0314-1006M	M10	1.50"	2.50"	0.75"	M10 x 1.5	1,200	0.20
39 S0314-1012M	M10	2.50"	4.50"	0.75"	M10 x 1.5	1,200	0.26
40 S0314-1304M	M12	1.00"	1.50"	1.00"	M12 x 1.75	2,150	0.30
41 S0314-1308M	M12	1.50"	3.25"	1.00"	M12 x 1.75	2,150	0.40
42 S0314-1315M	M12	3.00"	6.00"	1.00"	M12 x 1.75	2,150	0.56
43 S0314-1603M	M16	0.75"	1.00"	1.25"	M16 x 2.0	3,440	0.60
44 S0314-1605M	M16	1.75"	2.00"	1.25"	M16 x 2.0	3,440	0.64
45 S0314-1610M	M16	2.00"	4.00"	1.25"	M16 x 2.0	3,440	0.80
46 S0314-1615M	M16	3.00"	6.00"	1.25"	M16 x 2.0	3,440	1.00
47 S0314-2003M	M18	1.00"	1.00"	1.50"	M18 x 2.5	5,140	0.94
48 S0314-2005M	M18	1.75"	2.00"	1.50"	M18 x 2.5	5,140	1.12
49 S0314-2012M	M18	2.00"	4.50"	1.50"	M18 x 2.5	5,140	1.40
50 S0314-2015M	M18	3.00"	6.00"	1.50"	M18 x 2.5	5,140	1.58
51 S0314-2213M	M20	2.50"	5.00"	1.75"	M20 x 2.5	7,130	2.32
52 S0314-2504M	M24	1.38"	1.38"	2.00"	M24 x 3.0	9,370	2.56
53 S0314-2506M	M24	2.25"	2.50"	2.00"	M24 x 3.0	9,370	2.64
54 S0314-2515M	M24	3.00"	6.00"	2.00"	M24 x 3.0	9,370	3.44