


Thinner and longer jaws. Top functionality and torque.

Triple coated chrome finish (2 Ni + 1 Cr) for perfect chrome adherence and maximum rust resistance.

New and Improved Design:

- Dimensions 6" to 12"
- Up to 25% capacity
- Longer jaws
- Four thread knurl



Ergonomic handle design makes work easier and more efficient.

Metric measuring scale on jaws for easy jaws presetting and sizing of nuts, bolts, pipes, etc.

CHROME VANADIUM steel. Great resistance, minimum wear, unbeatable durability.

Identification code. Full traceability.

Non-protruding jaw shank. Great accessibility in tight spaces.

IREGA CODE	EAN	REF.	Length (mm.)	Opening (mm.)	Weight (gr.)
570100004005106	8410295021048	92/CE - 4"	115	13	52
570500006005106	8410295021062	92W/CE - 6"	161	24	155
570500008005106	8410295021086	92W/CE - 8"	207	30	310
570500010005106	8410295021109	92W/CE - 10"	259	34	490
570500012005103	8410295021123	92W/CE - 12"	311	39	805
570100015008103	8410295021154	92/CE - 15"	386	43,12	1.320
570100018008103	8410295021185	92/CE - 18"	462	53	2.040