


EA538MA-1-11B 裸圧着端子

◆丸型(R型)

◆材料…端子:無酸素銅(電気すずめっき)
スリーブ:無酸素銅管(電気すずめっき)



※ ~~は取扱中止商品です。~~

品番	型式	各部の寸法							電線抱合範囲			注)
		$\phi d2$	B	L	F	E	ϕD	ϕd	単線mm	撚線mm ²	AWG	
EA538MA 1	1.25 3	3.2	5.5	12.0	4.75	4.5	3.4	1.7	0.57~	0.25~	22-16	◎
EA538MA 2	1.25 4	4.3	8.0	15.6	7.1	4.5	3.4	1.7	1.44	1.65		◎
EA538MA 3	2 4	4.3	8.5	16.5	7.75	4.5	4.2	2.3	1.14~	1.04~	16-14	◎
EA538MA 4	2 5	5.3	9.5	17.0	7.75	4.5	4.2	2.3	1.82	2.63		◎
EA538MA 5	3.5 5S	5.3	9.6	20.0	9.2	6.0	5.0	3.0	1.82~2.4	2.63~4.6	12	○
EA538MA 6	5.5 4	4.3	9.5	19.5	8.25	6.5	5.6	3.4	1.82~	2.63~	12-10	◎
EA538MA 7	5.5 5	5.3	9.5	19.5	8.25	6.5	5.6	3.4	2.89	6.64		◎
EA538MA-7A	8-5	5.3	12.0	23.5	9.1	8.4	7.1	4.5	2.89~3.65	6.64~10.52	8	◎
EA538MA-8	8-6	6.4	12.0	23.5	9.1	8.4	7.1	4.5				◎
EA538MA 8A	8-8	8.4	15.0	29.5	13.6	8.4	7.1	4.5				◎
EA538MA 8B	14-6	6.4	12.0	27.5	11.5	10.0	9.0	5.8	—	10.52~16.78	6	◎
EA538MA 9	14-8	8.4	16.0	32.5	14.5	10.0	9.0	5.8				◎
EA538MA 9A	14-10	10.5	16.0	32.5	14.5	10.0	9.0	5.8				◎
EA538MA 10	22-8	8.4	16.5	33.3	13.05	12.0	11.5	7.7		16.78~26.66	4	◎
EA538MA 10A	22-10	10.5	17.5	36.3	15.55	12.0	11.5	7.7				◎
EA538MA 10B	22-12	13.0	22.0	42.3	19.3	12.0	11.5	7.7				◎
EA538MA 11	38-10	10.5	22	42.3	18.3	13.0	13.3	9.4		26.66~42.42	2	◎
EA538MA 11A	38-12	13.0	22.0	42.3	18.3	13.0	13.3	9.4				◎
EA538MA 11B	38-14	15.0	30.0	52.3	24.3	13.0	13.3	9.4				◎

注)◎:JIS規格品、UL、CSA登録品

○: UL、CSA登録品

◆取得規格

- ・日本工業規格 JIS C 2805(銅線用圧着端子)
- ・日本工業規格表示許可工場 許可番号570088(銅線用圧着端子)
- ・UL486A(WIRE CONNECTORS AND SOLDERING LUGS FOR COPPER CONDUCTORS)に適合
- ・UL ファイルNo.E44245にて承認
- ・CSA C22.2(CONSTRUCTION AND TEST OF WIRE CONNECTORS)に適合
- ・CSA ファイルNo.LR-28418にて承認