



Sledge Hammer Fibreglass Handle

SHFG

Sledge Hammers are designed for heavy demolition and hammering applications

Head

Forged from fine-grained special steel the heads are induction hardened 50-58 HRC for increased durability

Handle

Lightweight yet durable dual injection moulded fibreglass handle for controlled and balanced swing

Designed with a 25% wider neck, handles are covered with a polypropylene jacket for protection against overstrikes

TPR grip on handle absorbs shock and vibration and provides a non-slip grip

Handles securely attached to the hammer head using a tough epoxy adhesive ensuring that the head does not loosen even with rough use

Available in two types

- a. Short Handle – 16" (400mm)**
- b. Long Handle – 36" (900mm)**

UTILITY

- Driving in stakes
- Metal forming
- Setting bolts
- Demolition jobs

NEW!

BS 876

For material, hardness & performance

SANS 387:2014



ORDERING INFORMATION

CAT NR.	ORD NR.	HEAD WEIGHT		OVERALL LENGTH		BOX QTY.
		(LBS)	(KG)	(INCH)	(MM)	
SHORT HANDLE						
SHFG/2.5/16	36460	2.5	1.1	16	400	8
SHFG/4/16	36461	4	1.8	16	400	8

WARNING

Do not strike objects harder than 46 HRC. Striking items of a greater hardness is liable to cause fracture or chipping