



Tank Thermometer

Designed Specifically for Air Gas Industry
Tank Fillers for Steel and Aluminum* Tanks



Made In U.S.A.



Model 520-312F

- 13 lb. of Holding Power -- 35 Times It's Own Weight
- Single or Dual Max Hands Available at additional cost
- Certification Traceable to NIST Available
- Lexan Lens

SPECIFICATIONS

Model 520-350F	-20°F to +160°F
Model 520-315F	0°F to 150°F
Model 520-312F	0°F to 250°F
(EA722YV-1) Model 520-350C	-30°C to +70°C
(EA722YV-2) Model 520-315C	-15°C to +65°C
(EA722YV-3) Model 520-312C	-20°C to +120°C

Accuracy..... $\pm 2\%$ of full scale range.

Dimensions:

Length.....	4.25 in. (10.8 cm).
Width	2.25 in. (5.7 cm).
Height	0.56 in. (1.4 cm).
Weight	6 oz. (170 g).
Shipping weight	2 lb. (907 g).



ACCESSORIES

SSK Safety Strap Kit, which includes mounting hardware, hex key wrench, and safety straps.



Designed specifically for monitoring the filling of industrial tanks. The fast response and superior holding power make this thermometer the ultimate instrument for saving time and improving efficiency for monitoring tanks during filling. These thermometers are available with a certificate traceable to NIST.

Toll Free: 877-782-2329
Outside U.S.: 310-478-1134
Los Angeles, CA 90064-1482

web: <http://www.ptc1.com>
e-mail: sales@ptc1.com
FAX: 310-312-0826

