




ALL DIMENSIONS ARE FOR REFERENCE ONLY

DIMENSIONS ARE IN INCHES [MILLIMETERS]
UNLESS OTHERWISE NOTED



REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	INITIAL RELEASE	ND 4/2/2021	JRM 4/8/2021

SPECIFICATIONS

- OVERALL LENGTH ... 6.3 [159]
SHIPPING WEIGHT ... 1.05 POUNDS [0.48 KG]
COLOR BLACK
MATERIAL:
- 1. SUCTION CUP PVC - CLEAR
 - 2. BASE ASSEMBLY NYLON COMPOSITE - BLACK
 - 3. BASE KNOB NYLON COMPOSITE - BLACK
 - 4. BASE RIVET STEEL - BLACK OXIDED
 - 5. CARRIAGE BOLT STEEL - BLACK OXIDED
 - 6. KNUCKLE ASSEMBLY ZINC DIE CASTING PAINTED BLACK
 - 7. KNUCKLE KNOB ZINC DIE CASTING PAINTED BLACK
 - 8. AMPS BALL NYLON COMPOSITE - BLACK
 - 9. PORTAGRIP ASSEMBLY NYLON COMPOSITE - BLACK

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF PANAVISE PRODUCTS INC.. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF PANAVISE PRODUCTS INC IS PROHIBITED.

		UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL ± 1/64 ANGULAR: MACH ±1/2° BEND ± TWO PLACE DECIMAL: ±.01 THREE PLACE DECIMAL: ±.005	DRAWN	NAME	DATE	 PANAVISE® 7540 Colbert Drive, Reno, Nevada 89511-1225 Phone (775) 850-2900 Fax (775) 850-2929	
			CHECKED	ND	2APR21		
			ENG APPR.				
			MFG APPR.				
			Q.A.				
		INTERPRET GEOMETRIC TOLERANCING PER: ASME 14.5M -2009	COMMENTS:	TITLE: PORTAGRIP SUCTION CUP W/ 809-AMP SPEC SHEET			
		MATERIAL SEE NOTES					
NEXT ASSY	USED ON	FINISH SEE NOTES					
APPLICATION		DO NOT SCALE DRAWING					
			SIZE B			DWG. NO. 15508-SP	REV A
			SCALE: 1:2		WEIGHT:	SHEET 1 OF 1	