

Adhesive Backed Disc Magnets

- 3M 486 adhesive backing for best adhesion
- Quick release tab for fast and effective liner removal
- Strongest magnet material available
- Maximum operating temperature 80°C



Product Number	Height (mm)	Polarity	Adhesive	Units per Pack	Coating	Dia. D (mm)	Holding Force (kg)	Material Grade	Product Weight per Pack (g)
N850N	1	North	3M 468 Adhesive with quick release Tab	50	Nickel Plated	6	0.3	N42	11.65
N850S	1	South	3M 468 Adhesive with quick release Tab	50	Nickel Plated	6	0.3	N42	11.65
N851N	1	North	3M 468 Adhesive with quick release Tab	50	Nickel Plated	8	0.4	N42	18.76
N851S	1	South	3M 468 Adhesive with quick release Tab	50	Nickel Plated	8	0.4	N42	18.76
N852N EA781EE-33	1	North	3M 468 Adhesive with quick release Tab	50	Nickel Plated	10	0.5	N42	30
N852S EA781EE-43	1	South	3M 468 Adhesive with quick release Tab	50	Nickel Plated	10	0.5	N42	30
N853N	1	North	3M 468 Adhesive with quick release Tab	50	Nickel Plated	12	0.65	N42	41.66
N853S	1	South	3M 468 Adhesive with quick release Tab	50	Nickel Plated	12	0.65	N42	41.66
N854N EA781EE-35	1	North	3M 468 Adhesive with quick release Tab	50	Nickel Plated	15	0.8	N42	67.5
N854S EA781EE-45	1	South	3M 468 Adhesive with quick release Tab	50	Nickel Plated	15	0.8	N42	67.5