





























EA819GF-102～-344 研磨キャップ(アルミナ)+マンドレル組合せ表

研磨キャップ						マンドレル					
EA品番	砥粒	粒度	直径(mm)	幅(mm)	先端形状	EA品番	直径(mm)	幅(mm)	軸径×軸長(mm)	最大回転数(rpm)	先端形状
EA819GF-102	アルミナ	80	5	10		EA819GF-181	5	10	3x25	95,000	
EA819GF-103		150									
EA819GF-104		320									
EA819GF-111	アルミナ	60	7	12		EA819GF-182	7	12	3x25	65,000	
EA819GF-112		80									
EA819GF-113		150									
EA819GF-114		320									
EA819GF-121	アルミナ	60	10	15		EA819GF-183	10	15	3x25	45,000	
EA819GF-122		80									
EA819GF-123		150									
EA819GF-124		320									
EA819GF-131	アルミナ	60	13	17		EA819GF-184	13	17	3x25	35,000	
EA819GF-132		80									
EA819GF-133		150									
EA819GF-134		320									
EA819GF-141	アルミナ	60	16	26		EA819GF-185	16	26	3x25	18,000	
EA819GF-142		80									
EA819GF-143		150									
EA819GF-144		320									
EA819GF-202	アルミナ	80	5	11		EA819GF-281	5	11	3x25	95,000	
EA819GF-203		150									
EA819GF-204		320									
EA819GF-211	アルミナ	60	7	13		EA819GF-282	7	13	3x25	65,000	
EA819GF-212		80									
EA819GF-213		150									
EA819GF-214		320									
EA819GF-221	アルミナ	60	10	15		EA819GF-283	10	15	3x25	45,000	
EA819GF-222		80									
EA819GF-223		150									
EA819GF-224		320									
EA819GF-231	アルミナ	60	13	19		EA819GF-284	13	19	3x25	35,000	
EA819GF-232		80									
EA819GF-233		150									
EA819GF-234		320									
EA819GF-241	アルミナ	60	16	26		EA819GF-285	16	26	3x25	18,000	
EA819GF-242		80									
EA819GF-243		150									
EA819GF-244		320									
EA819GF-312	アルミナ	80	7	13		EA819GF-382	7	13	3x25	65,000	
EA819GF-313		150									
EA819GF-314		320									
EA819GF-321	アルミナ	60	10	15		EA819GF-383	10	15	3x25	45,000	
EA819GF-322		80									
EA819GF-323		150									
EA819GF-324		320									
EA819GF-331	アルミナ	60	13	19		EA819GF-384	13	19	3x25	35,000	
EA819GF-332		80									
EA819GF-333		150									
EA819GF-334		320									
EA819GF-341	アルミナ	60	16	26		EA819GF-385	16	26	3x25	18,000	
EA819GF-342		80									
EA819GF-343		150									
EA819GF-344		320									