Instruction Part Number P17080 Issue 3

How to use and care for your Quickset Adjustable Torque Screwdriver

Tool Specification

Models: All models

(QS Minor: 0.2 - 1.2 Nm, QS 6: 1.0 - 6.0 Nm, QS 9: 4.0 - 9.0 Nm)

Accuracy: +/- 6% of Torque Setting

ISO 6789 Class: Type 2, Class D

Calibration Period: Every 12 Months or 5000 cycles (minimum)

Mechanism: Slipping - Incorrect tightening is impossible

an angle of 60° before resetting. At the set torque, the handle rotates through



Safety & Maintenance

- ✓ This Torque Tool is a precision instrument and should be used for its intended purpose only
- Only hold the tool using the handgrip
- Always ensure that the tool is in correct alignment with the fastener
- ✓ Torque tools should be regularly calibrated and inspected to ensure correct operation
- Ensure the tool is clean and free from oil, grease and water before use
- Do not use extension bars to increase the leverage of the handle
- Never dip into cleaning fluid or petroleum

How to adjust your Torque Screwdriver

To adjust the torque setting:

down on the black adjusting knob. Engage the adjusting mechanism by pressing

To increase torque:

torque is selected on the calibrated scale. Rotate the handle clockwise until the required



To reduce torque:

setting, then increase torque to the required When adjusting, always approach the required Rotate the handle anti clockwise passed your torque from a lower setting.



To increase leverage:

screwdrivers, provides extra leverage when required. (Order Code P29530). Optional lock on T-Bar for larger models of the end of the handle. This fits into the ¼" Square Drive (SD) in



To use Torque Screwdriver:

After use, set the screwdriver at the lowest setting for use with sockets, screwdriver bits and blades. The Quickset Screwdriver is designed

Servicing Information

ensure it continues to perform correctly. Regular servicing of your Torque Tool by competent personnel is important to