

Utility

Neodymium

Rubber Covered Neodymium Pots

- Santoprene Rubber coating for scratch-free clamping
- Neodymium Magnets (NdFeB) inside for maximum holding forces
- Extremely good shear forces - high resistance to sliding
- Protects surfaces such as lacquered mild steel car body work
- Maximum recommended operating temperature is 60°C

With Threaded Neck

| Product Number | Diameter mm | Thickness mm | Overall Height mm | Thread Length mm | Thread Size | Holding Force kg | Units / Pack |
|----------------|-------------|--------------|-------------------|------------------|-------------|------------------|--------------|
| E851 | 22 | 6 | 12.5 | 6.5 | M4 | 5 | 2 |
| E853 | 43 | 6 | 21 | 15 | M6 | 8.5 | 2 |
| E854 | 66 | 8.5 | 23.5 | 15 | M8 | 18 | 2 |
| E855 | 88 | 8.5 | 23.5 | 15 | M8 | 42 | 2 |

