


図面／規格  
【六角ナット（１種鉄M 2 5 以上黒皮）】



EA949LS-

|      | 呼び   | 並目   | m    |            | s    |            |
|------|------|------|------|------------|------|------------|
|      |      |      | 基準寸法 | 許容差        | 基準寸法 | 許容差        |
| 102A | M2   | 0.4  | 1.6  | 0<br>-0.25 | 4    | 0<br>-0.2  |
|      | M2.3 | 0.4  | 1.8  |            | 4.5  |            |
|      | M2.5 | 0.45 | 2    |            | 5    |            |
|      | M2.6 | 0.45 | 2    |            | 5    |            |
| 103A | M3   | 0.5  | 2.4  | 0<br>-0.30 | 5.5  | 0<br>-0.2  |
|      | M3.5 | 0.6  | 2.8  |            | 6    |            |
| 104A | M4   | 0.7  | 3.2  |            | 7    |            |
|      | M4.5 | 0.75 | 3.6  |            | 8    |            |
| 105A | M5   | 0.8  | 4    | 0<br>-0.30 | 8    | 0<br>-0.25 |
| 106A | M6   | 1.0  | 5    |            | 10   |            |
|      | M7   | 1.0  | 5.5  |            | 11   |            |
| 108A | M8   | 1.25 | 6.5  | 0<br>-0.58 | 13   | 0<br>-0.7  |
|      | M9   | 1.25 | 8    |            | 17   |            |
| 110A | M10  | 1.5  | 8    |            | 17   |            |
| 112A | M12  | 1.75 | 10   |            | 19   |            |
| 114  | M14  | 2.0  | 11   | ±0.8       | 22   | 0<br>-0.8  |
| 116  | M16  | 2.0  | 13   |            | 24   |            |
| 118  | M18  | 2.5  | 15   |            | 27   |            |

|     | 呼び  | 並目  | m    |      | s    |           |
|-----|-----|-----|------|------|------|-----------|
|     |     |     | 基準寸法 | 許容差  | 基準寸法 | 許容差       |
| 120 | M20 | 2.5 | 16   | ±0.9 | 30   | 0<br>-0.8 |
| 122 | M22 | 2.5 | 18   |      | 32   | 0<br>-1.0 |
| 124 | M24 | 3.0 | 19   |      | 36   |           |
|     | M25 | 3.0 | 19   |      | 36   |           |
|     | M27 | 3.0 | 22   | ±1.0 | 41   | 0<br>-1.0 |
|     | M30 | 3.5 | 24   |      | 46   |           |
|     | M33 | 3.5 | 26   |      | 50   |           |
|     | M36 | 4.0 | 29   |      | 55   |           |
|     | M39 | 4.0 | 31   | ±1.2 | 60   | 0<br>-1.2 |
|     | M42 | 4.5 | 34   |      | 65   |           |
|     | M45 | 4.5 | 36   |      | 70   |           |
|     | M48 | 5.0 | 38   |      | 75   |           |
|     | M52 | 5.0 | 42   | ±1.5 | 80   | 0<br>-1.4 |
|     | M56 | 5.5 | 45   |      | 85   |           |
|     | M60 | 5.5 | 48   |      | 90   |           |
|     | M64 | 6.0 | 51   |      | 95   |           |
|     | M68 | 6.0 | 54   |      | 100  |           |