### WEICON

#### WEICONLOCK®

# WEICONLOCK® AN 302-43 Threadlocking



#### Threadlocking | drinking water and DVGW approval

- · higher viscosity
- · medium strength
- · disassembly with normal tools

#### Technische Daten

Colour		blue
For thread connections up to		M 36
Gap bridging up to max.		0,25 mm
Breakaway torque		17 - 22 Nm
Prevail torque		8 - 12 Nm
Shear strength Nmm² (DIN 54452)		9 - 13 N/mm²
Handling strength		10 - 20 min.
Final strength	(100 % strength)	1-3 h
Temperature resistance		-60°C to +200°C
IMPA Code		812912/13/14
ISSA Code		75.628.06/04/05

## **Anaerobe Kleb- und Dichtstoffe**

#### Surface pre-treatment

To achieve optimum results, the mounting parts should be degreased and cleaned, e.g. with WEICON Surface (roughen the surfaces, if required). WEICONLOCK can also be used on uncleaned surfaces, e.g. screws as delivered. However, the cleaner the surface, the better the results achieved.

#### **Processing**

WEICONLOCK is applied evenly straight from the Pen with the help of the dosing tip; avoid direct contact between dosing tip /metal. For sealing applications, apply WEICONLOCK to the thread in circles. Assemble parts and screw tight. Do not pour any WEICONLOCK back into the bottle that has already come into contact with metal. Even extremely small metal particles cause the adhesive to cure inside the bottle. Therefore, in serial production, the use of dosing devices is recommended.

#### **Storage**

WEICONLOCK has a shelf life of at least 24 months, when stored at room temperature in closed original container. Protect from heat sources and direct sunlight. The air contained in the Pen keeps WEICONLOCK liquid.

#### Safety and health

When using WEICON products, the physical, safety-related, toxicological and ecological data and regulations in our EC safety data sheets (www.weicon.com) must be observed.

WEICONLOCK® AN 302-43 Threadlocking, 3

#### **Accessories**

30700200 Activator F, 200 ml, green 30955172 Dosing Tip, 1 PCE

#### Available sizes:

30243003

002 10000	ml, blue
30243020	WEICONLOCK® AN 302-43 Threadlocking, 20 ml. blue
30243050	WEICONLOCK® AN 302-43 Threadlocking, 50 ml. blue
30243103	WEICONLOCK® AN 302-43 Threadlocking, 3 ml. blue
30243110	WEICONLOCK® AN 302-43 Threadlocking, 10
30243150	ml, blue WEICONLOCK® AN 302-43 Threadlocking, 50
30243200	ml, blue WEICONLOCK® AN 302-43 Threadlocking, 200
30243250	ml, blue WEICONLOCK® AN 302-43 Threadlocking, 250
30243300	ml, blue WEICONLOCK® AN 302-43 Threadlocking, 300

The specifications and recommendations given in this technical data sheet must not be seen as guaranteed product characteristics. They are based on our laboratory tests and on practical experience. Since individual application conditions are beyond our knowledge, control and responsibility, this information is provided without any obligation. We do guarantee the continuously high quality of our products. However, own adequate laboratory and practical tests to find out if the product in question meets the requested properties are recommended. A claim cannot be derived from them. The user bears the requested properties are recommended. A claim cannot be derived from them.

ml. blue

# WEICONLOCK® AN 302-43 Threadlocking

### WEICONLOCK® **Anaerobe Kleb- und Dichtstoffe**



Note
The specifications and recommendations given in this technical data sheet must not be seen as guaranteed product characteristics. They are based on our laboratory tests and on practical experience. Since individual application conditions are beyond our knowledge, control and responsibility, this information is provided without any obligation. We do guarantee the continuously high quality of our products. However, own adequate laboratory and practical tests to find out if the product in question meets the requested properties are recommended. A claim cannot be derived from them. The user bears the only responsibility for non-appropriate or other than specified applications.