



品番	仕上/色	H	L	B	P ₁	P ₂	P ₃	P ₄	P ₅	P ₆	P ₇	P ₈	耐荷重N/1ヶ	耐荷重kgf/1ヶ
EA951E-21	アンバー	86	69	15	58	27	-	-	75	26	-	-	147 N/1ヶ	15 kgf/1ヶ
EA951E-22	アンバー	120	100	15	85	43	-	-	106	42	-	-	196 N/1ヶ	20 kgf/1ヶ
EA951E-23	アンバー	180.5	148.5	15	131	71	50	-	162.5	72.5	51.5	-	245 N/1ヶ	25 kgf/1ヶ
EA951E-24	アンバー	240	199	18	176	91	59	-	217	92	60	-	274.4N/1ヶ	28 kgf/1ヶ
EA951E-25	アンバー	301	238.5	20	206.5	92.5	60.5	-	269	95	63	-	343 N/1ヶ	35 kgf/1ヶ

※単位:mm



品番	d	取付穴数N	質量	C ₁	C ₂	C ₃	C ₄	C ₅	C ₆	C ₇	C ₈	R	付属ねじサイズ
EA951E-21	4	4	40g	-	-	(9)	(5)	-	-	(12)	(5)	(25)	3.5×16 (3本)、3.5×25 (1本)
EA951E-22	4	4	60g	-	-	(10)	(5)	-	-	(13)	(5)	(25)	3.5×16 (3本)、3.5×25 (1本)
EA951E-23	4	6	110g	-	(14)	(12)	(5)	-	(15)	(13)	(5)	(30)	3.5×16 (2本)、3.5×20 (1本)、3.5×25 (1本)、3.8×32 (2本)
EA951E-24	4	6	200g	-	(16)	(13)	(8)	-	(16)	(14)	(7.5)	(35)	3.5×16 (2本)、3.5×20 (1本)、3.5×25 (1本)、3.8×32 (2本)
EA951E-25	4	6	310g	-	(19.5)	(17)	(8)	-	(19)	(17.5)	(9)	(35)	3.5×16 (1本)、3.5×25 (2本)、3.5×32 (1本)、3.8×38 (2本)