


●スラスト玉軸受



動等価アキシャル荷重
 $P_a = F_a$
静等価アキシャル荷重
 $P_{0a} = F_a$

d 10～50mm

主 要 寸 法				基本動 定格荷重	基本静 定格荷重	基本動 定格荷重	基本静 定格荷重	許容回転速度		呼び番号	寸法			取付関係寸法			質 量	EA品番
mm				kN		kgf		min ⁻¹			mm			mm			kg	
d	D	T	$r_s \min^{1)}$	C_a	C_{0a}	C_a	C_{0a}	グリース潤滑	油潤滑		$d_{1s \max}^{2)}$	$D_{1s \min}^{3)}$	t	d_a 最小	D_a 最大	r_{as} 最大	(参考)	
10	24	9	0.3	10.0	14.0	1 020	1 420	6 700	9 500	51100 51200	24	11	2.5	18	16	0.3	0.021	EA966AD-0
	26	11	0.6	12.7	17.1	1 290	1 740	5 800	8 300		26	12	3.3	20	16	0.6	0.03	EA966AE-0
12	26	9	0.3	10.3	15.4	1 050	1 570	6 400	9 200	51101 51201	26	13	2.5	20	18	0.3	0.023	EA966AD-1
	28	11	0.6	13.2	19.0	1 340	1 940	5 600	8 000		28	14	3.3	22	18	0.6	0.034	EA966AE-1
15	28	9	0.3	10.5	16.8	1 070	1 710	6 200	8 800	51102 51202	28	16	2.5	23	20	0.3	0.024	EA966AD-2
	32	12	0.6	16.6	24.8	1 690	2 530	5 000	7 100		32	17	3.5	25	22	0.6	0.046	EA966AE-2
17	30	9	0.3	10.8	18.2	1 100	1 850	6 000	8 500	51103 51203	30	18	2.5	25	22	0.3	0.026	EA966AD-3
	35	12	0.6	17.2	27.3	1 750	2 780	4 800	6 800		35	19	3.5	28	24	0.6	0.054	EA966AE-3
20	35	10	0.3	14.2	24.7	1 450	2 520	5 200	7 500	51104 51204	35	21	2.5	29	26	0.3	0.04	EA966AD-4
	40	14	0.6	22.3	37.5	2 270	3 850	4 100	5 900		40	22	4.1	32	28	0.6	0.081	EA966AE-4
25	42	11	0.6	19.6	37.0	1 990	3 800	4 600	6 500	51105 51205	42	26	3	35	32	0.6	0.06	EA966AD-5
	47	15	0.6	27.8	50.5	2 830	5 150	3 700	5 300		47	27	4.3	38	34	0.6	0.111	EA966AE-5
30	47	11	0.6	20.4	42.0	2 080	4 300	4 300	6 200	51106 51206	47	32	3	40	37	0.6	0.069	EA966AD-6
	52	16	0.6	29.3	58.0	2 990	5 950	3 400	4 900		52	32	5	43	39	0.6	0.139	EA966AE-6
35	52	12	0.6	20.4	44.5	2 080	4 550	3 900	5 600	51107 51207	52	37	3.5	45	42	0.6	0.085	EA966AD-7
	62	18	1	39.0	78.0	4 000	7 950	2 900	4 200		62	37	5.2	51	46	1	0.215	EA966AE-7
40	60	13	0.6	26.9	63.0	2 740	6 400	3 500	5 000	51108 51208	60	42	3.8	52	48	0.6	0.125	EA966AD-8
	68	19	1	47.0	98.5	4 800	10 000	2 700	3 900		68	42	5.5	57	51	1	0.276	EA966AE-8
45	65	14	0.6	27.9	69.0	2 840	7 050	3 200	4 600	51109 51209	65	47	4	57	53	0.6	0.148	EA966AD-9
	73	20	1	48.0	105	4 850	10 700	2 600	3 700		73	47	6	62	56	1	0.317	EA966AE-9
50	70	14	0.6	28.8	75.5	2 930	7 700	3 100	4 500	51110 51210	70	52	4	62	58	0.6	0.161	EA966AD-10
	78	22	1	48.5	111	4 950	11 400	2 400	3 400		78	52	7	67	61	1	0.378	EA966AE-10
55	78	16	0.6	35.0	93.0	3 550	9 500	2 800	4 000	51111	78	57	5	69	64	0.6	0.226	EA966AD-11
60	85	17	1	41.5	113	4 200	11 500	2 600	3 700	51112	85	62	5	75	70	1	0.296	EA966AD-12
65	90	18	1	41.5	117	4 250	12 000	2 400	3 500	51113	90	67	5.5	80	75	1	0.338	EA966AD-13
70	95	18	1	43.0	127	4 400	12 900	2 400	3 400	51114	95	72	5.5	85	80	1	0.356	EA966AD-14
75	100	19	1	44.5	136	4 550	13 900	2 200	3 200	51115	100	77	6	90	85	1	0.399	EA966AD-15

注 1) 面取寸法 r の最小許容寸法である。 2) 軸軌道盤外径 d_1 の最大許容寸法である。 3) ハウジング軌道盤内径 D_1 の最小許容寸法である。